

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P751556

Luminaire Tested: LD4D65D010-EU4DR3555659040-4LBCSSQMMS

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P751556
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D65D010-EU4DR3555659040-4LBCSSQMMS
Description: 4 INCH SQAURE SHALLOW CAST MATTE METALLIC SILVER TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6469.6 lumens
Efficiency: N/A
Efficacy: 88.9 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 72.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P751556

CATALOG NUMBER: LD4D65D010-EU4DR3555659040-4LBCSSQMMS

Luminous Intensity Polar Plot





TEST NUMBER: P751556

CATALOG NUMBER: LD4D65D010-EU4DR3555659040-4LBCSSQMMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20								
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	99	98	98	96	96	96	92	92																
	1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	98	96	96	96	92	91	91	89	89	89	84	84																
	2	110	106	103	101	108	105	102	99	102	99	97	99	97	95	96	95	93	92	92	92	89	89	89	86	86	86	81	81																
	3	106	101	97	94	105	100	96	93	97	95	92	95	93	91	93	91	89	88	88	88	86	86	84	84	84	81	81	81																
	4	103	97	92	89	101	96	92	89	94	90	88	92	89	87	90	88	86	84	84	84	82	82	81	81	81	78	78	78																
	5	99	93	88	85	98	92	87	84	90	86	84	89	85	83	87	84	82	81	81	81	79	79	79	76	76	76	75	75																
	6	96	89	84	81	94	88	84	81	87	83	80	85	82	80	84	81	79	78	78	78	76	76	75	75	75	72	72	72																
	7	93	85	81	78	91	85	80	77	84	80	77	83	79	77	82	79	76	75	75	75	74	74	73	73	73	70	70	70																
	8	90	82	78	74	88	82	77	74	81	77	74	80	76	74	79	76	73	72	72	72	71	71	71	70	70	70	68	68																
	9	87	79	75	72	86	79	75	72	78	74	71	77	74	71	77	73	71	70	70	70	69	69	69	68	68	68	66	66																
	10	84	77	72	69	83	76	72	69	76	72	69	75	71	69	74	71	69	68	68	68	67	67	67	66	66	66	64	64																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1944951
5°	1899252
10°	1711735
15°	1328582
20°	753553
25°	293168
30°	109371
35°	59956
40°	39180
45°	23858
50°	15179
55°	10725
60°	7845
65°	4266
70°	319
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 23858 cd/sqm



TEST NUMBER: P751556

CATALOG NUMBER: LD4D65D010-EU4DR3555659040-4LBCSSQMMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1592.6	24.6
10°-20°	3109.5	48.1
20°-30°	1268.2	19.6
30°-40°	303.5	4.7
40°-50°	126.5	2.0
50°-60°	52.3	0.8
60°-70°	16.4	0.3
70°-80°	0.4	0.0
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5970.3	92.3
0°-40°	6273.8	97.0
0°-60°	6452.6	99.7
0°-90°	6469.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6469.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	17801	
5°	17317	###
15°	11745	3109
25°	2432	1268
35°	450	303
45°	154	126
55°	56	52
65°	16	16
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P751556

CATALOG NUMBER: LD4D65D010-EU4DR3555659040-4LBCSSQMMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	17801.0
2.5°	17694.2
5°	17316.6
7.5°	16563.3
10°	15428.5
12.5°	13830.6
15°	11745.4
17.5°	9195.1
20°	6480.9
22.5°	4132.6
25°	2431.8
27.5°	1374.6
30°	866.9
32.5°	608.7
35°	449.5
37.5°	347.5
40°	274.7
42.5°	211.6
45°	154.4
47.5°	115.5
50°	89.3
52.5°	70.9
55°	56.3
57.5°	45.6
60°	35.9
62.5°	26.2
65°	16.5
67.5°	5.8
70°	1.0
72.5°	1.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	1.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)