

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P741758

Luminaire Tested: LD4D08D010-EU4DR700210IC9035-4LBSQW1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P741758
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D08D010-EU4DR700210IC9035-4LBSQW1MW
Description: 4 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 655.3 lumens
Efficiency: N/A
Efficacy: 73.6 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 8.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P741758
CATALOG NUMBER: LD4D08D010-EU4DR700210IC9035-4LBSQW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P741758

CATALOG NUMBER: LD4D08D010-EU4DR700210IC9035-4LBSQW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	88	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	80503
5°	78113
10°	75932
15°	74927
20°	69973
25°	52562
30°	37168
35°	13165
40°	6918
45°	7371
50°	7632
55°	7791
60°	7823
65°	7653
70°	7220
75°	6712
80°	5977
85°	4764

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 7829 cd/sqm



TEST NUMBER: P741758

CATALOG NUMBER: LD4D08D010-EU4DR700210IC9035-4LBSQW1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	67.2	10.3
10°-20°	184.2	28.1
20°-30°	202.9	31.0
30°-40°	77.5	11.8
40°-50°	36.6	5.6
50°-60°	36.4	5.6
60°-70°	29.1	4.4
70°-80°	16.8	2.6
80°-90°	4.5	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	454.4	69.3
0°-40°	531.9	81.2
0°-60°	604.9	92.3
0°-90°	655.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	655.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	737	
5°	712	67
15°	662	184
25°	436	203
35°	99	78
45°	48	37
55°	41	36
65°	30	29
75°	16	17
85°	4	5
90°	0	



TEST NUMBER: P741758

CATALOG NUMBER: LD4D08D010-EU4DR700210IC9035-4LBSQW1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	736.8
2.5°	729.1
5°	712.2
7.5°	698.0
10°	684.4
12.5°	672.9
15°	662.4
17.5°	637.4
20°	601.8
22.5°	525.1
25°	436.0
27.5°	379.6
30°	294.6
32.5°	190.3
35°	98.7
37.5°	53.3
40°	48.5
42.5°	48.2
45°	47.7
47.5°	46.6
50°	44.9
52.5°	42.9
55°	40.9
57.5°	38.5
60°	35.8
62.5°	32.8
65°	29.6
67.5°	26.1
70°	22.6
72.5°	19.1
75°	15.9
77.5°	12.5
80°	9.5
82.5°	6.6
85°	3.8
87.5°	1.5
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)