

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P752115

Luminaire Tested: LD4D65D010-EU4DR7055659050-4LBCSSQMMS

Issue Date: 1/30/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P752115  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-76)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 1/30/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D65D010-EU4DR7055659050-4LBCSSQMMS  
Description: 4 INCH SQAURE SHALLOW CAST MATTE METALLIC SILVER TRIM, WITH 70° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7038.3 lumens  
Efficiency: N/A  
Efficacy: 96.7 lumens/watt  
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.04  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 72.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P752115  
CATALOG NUMBER: LD4D65D010-EU4DR7055659050-4LBCSSQMMS

### Luminous Intensity Polar Plot





TEST NUMBER: P752115

CATALOG NUMBER: LD4D65D010-EU4DR7055659050-4LBCSSQMMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	95	94	93
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85
3	101	94	88	84	99	92	87	83	90	85	82	87	84	81	85	82	79	78
4	95	87	81	76	93	86	80	76	83	78	75	81	77	74	79	76	73	71
5	89	80	74	69	88	79	73	69	78	72	68	76	71	68	74	70	67	65
6	84	75	68	63	83	74	68	63	72	67	63	71	66	62	69	65	62	60
7	80	69	63	58	78	69	62	58	67	62	58	66	61	57	65	61	57	56
8	75	65	58	54	74	64	58	54	63	57	53	62	57	53	61	56	53	51
9	71	61	54	50	70	60	54	50	59	53	50	58	53	49	57	53	49	48
10	67	57	50	46	66	56	50	46	55	50	46	55	50	46	54	49	46	44

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	606965
5°	605445
10°	604136
15°	603967
20°	598061
25°	561803
30°	500844
35°	399335
40°	265163
45°	158520
50°	82185
55°	43203
60°	15275
65°	259
70°	0
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 158520 cd/sqm



TEST NUMBER: P752115

CATALOG NUMBER: LD4D65D010-EU4DR7055659050-4LBCSSQMMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	525.0	7.5
10°-20°	1505.6	21.4
20°-30°	2124.0	30.2
30°-40°	1833.6	26.1
40°-50°	821.1	11.7
50°-60°	215.0	3.1
60°-70°	14.0	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4154.6	59.0
0°-40°	5988.2	85.1
0°-60°	7024.3	99.8
0°-90°	7038.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7038.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5555	
5°	5520	525
15°	5339	1506
25°	4660	2124
35°	2994	1834
45°	1026	821
55°	227	215
65°	1	14
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P752115

CATALOG NUMBER: LD4D65D010-EU4DR7055659050-4LBCSSQMMS

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	5555.2
2.5°	5549.2
5°	5520.2
7.5°	5496.2
10°	5445.3
12.5°	5399.3
15°	5339.4
17.5°	5270.5
20°	5143.6
22.5°	4934.8
25°	4660.1
27.5°	4341.4
30°	3969.8
32.5°	3515.3
35°	2993.9
37.5°	2418.5
40°	1859.1
42.5°	1412.5
45°	1025.9
47.5°	707.3
50°	483.5
52.5°	333.7
55°	226.8
57.5°	136.9
60°	69.9
62.5°	22.0
65°	1.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)