

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P754258

Luminaire Tested: LD4D80BD010-EU4DR6070959027-4LBSQW1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P754258
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D80BD010-EU4DR6070959027-4LBSQW1MW
Description: 4 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6659.1 lumens
Efficiency: N/A
Efficacy: 84.4 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 78.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P754258

CATALOG NUMBER: LD4D80BD010-EU4DR6070959027-4LBSQW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P754258

CATALOG NUMBER: LD4D80BD010-EU4DR6070959027-4LBSQW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			93																
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86			86																
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80			80																
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75			75																
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70			70																
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66			66																
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62			62																
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59			59																
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55			55																
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53			53																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	864100
5°	885355
10°	896047
15°	853600
20°	752611
25°	608735
30°	411760
35°	206330
40°	33475
45°	32758
50°	33418
55°	33926
60°	34854
65°	35652
70°	36482
75°	36938
80°	35613
85°	29711

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 36938 cd/sqm



TEST NUMBER: P754258

CATALOG NUMBER: LD4D80BD010-EU4DR6070959027-4LBSQW1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	771.5	11.6
10°-20°	2087.4	31.3
20°-30°	2245.8	33.7
30°-40°	976.2	14.7
40°-50°	164.0	2.5
50°-60°	159.4	2.4
60°-70°	136.3	2.0
70°-80°	91.2	1.4
80°-90°	27.3	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5104.7	76.7
0°-40°	6080.9	91.3
0°-60°	6404.3	96.2
0°-90°	6659.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6659.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7909	
5°	8072	772
15°	7546	2087
25°	5049	2246
35°	1547	976
45°	212	164
55°	178	159
65°	138	136
75°	88	91
85°	24	27
90°	0	



TEST NUMBER: P754258

CATALOG NUMBER: LD4D80BD010-EU4DR6070959027-4LBSQW1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	7908.6
2.5°	8130.9
5°	8072.3
7.5°	8090.8
10°	8076.4
12.5°	7909.6
15°	7546.3
17.5°	7058.5
20°	6472.8
22.5°	5846.0
25°	5049.4
27.5°	4038.7
30°	3263.7
32.5°	2515.4
35°	1546.9
37.5°	661.8
40°	234.7
42.5°	216.1
45°	212.0
47.5°	204.8
50°	196.6
52.5°	187.3
55°	178.1
57.5°	168.8
60°	159.5
62.5°	149.2
65°	137.9
67.5°	126.6
70°	114.2
72.5°	100.9
75°	87.5
77.5°	72.0
80°	56.6
82.5°	40.1
85°	23.7
87.5°	8.2
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)