

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P752389

Luminaire Tested: LD4D70BD010-EU4DR4070959030-4LBCSSQMW

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P752389
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-28)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D70BD010-EU4DR4070959030-4LBCSSQMW
Description: 4 INCH SQAURE SHALLOW CAST MATTE WHITE TRIM, WITH 40° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6703.8 lumens
Efficiency: N/A
Efficacy: 100.7 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.6
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 66.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P752389

CATALOG NUMBER: LD4D70BD010-EU4DR4070959030-4LBCSSQMW

Luminous Intensity Polar Plot





TEST NUMBER: P752389

CATALOG NUMBER: LD4D70BD010-EU4DR4070959030-4LBCSSQMW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	97	96																			
2	110	106	103	100	108	105	102	99	102	99	97	99	97	95	96	95	93	92																			
3	106	101	97	94	104	100	96	93	97	94	92	95	93	90	93	91	89	88																			
4	102	97	92	89	101	95	91	88	93	90	87	92	89	86	90	87	85	84																			
5	99	92	88	84	97	91	87	84	90	86	83	88	85	83	87	84	82	81																			
6	95	88	84	80	94	88	83	80	86	82	80	85	82	79	84	81	79	77																			
7	92	85	80	77	91	84	80	77	83	79	76	82	79	76	81	78	76	74																			
8	89	82	77	74	88	81	77	74	80	76	73	79	76	73	78	75	73	72																			
9	86	79	74	71	85	78	74	71	77	73	71	76	73	70	76	72	70	69																			
10	83	76	71	68	82	75	71	68	75	71	68	74	70	68	73	70	68	67																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1705364
5°	1697071
10°	1604106
15°	1363692
20°	929450
25°	387804
30°	121937
35°	56674
40°	31336
45°	14370
50°	6969
55°	3829
60°	1989
65°	698
70°	288
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 14370 cd/sqm



TEST NUMBER: P752389

CATALOG NUMBER: LD4D70BD010-EU4DR4070959030-4LBCSSQMW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1444.8	21.6
10°-20°	3236.8	48.3
20°-30°	1620.2	24.2
30°-40°	297.0	4.4
40°-50°	81.9	1.2
50°-60°	19.3	0.3
60°-70°	3.7	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6301.8	94.0
0°-40°	6598.8	98.4
0°-60°	6700.0	99.9
0°-90°	6703.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6703.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	15608	
5°	15473	###
15°	12056	3237
25°	3217	1620
35°	425	297
45°	93	82
55°	20	19
65°	3	4
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P752389

CATALOG NUMBER: LD4D70BD010-EU4DR4070959030-4LBCSSQMW

CANDELA DISTRIBUTION (FULL):

0°	
0°	15608.2
2.5°	15585.4
5°	15473.2
7.5°	15115.8
10°	14458.4
12.5°	13433.5
15°	12055.8
17.5°	10264.1
20°	7993.7
22.5°	5449.8
25°	3216.8
27.5°	1700.5
30°	966.5
32.5°	624.6
35°	424.9
37.5°	303.6
40°	219.7
42.5°	150.4
45°	93.0
47.5°	59.3
50°	41.0
52.5°	29.2
55°	20.1
57.5°	12.8
60°	9.1
62.5°	5.5
65°	2.7
67.5°	1.8
70°	0.9
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)