

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P754349

Luminaire Tested: LD4D80BD010-EU4DR6570959030-4LBSQW1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P754349
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D80BD010-EU4DR6570959030-4LBSQW1MW
Description: 4 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5999.4 lumens
Efficiency: N/A
Efficacy: 76.0 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 78.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P754349

CATALOG NUMBER: LD4D80BD010-EU4DR6570959030-4LBSQW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P754349

CATALOG NUMBER: LD4D80BD010-EU4DR6570959030-4LBSQW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93								
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87								
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80								
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75								
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69								
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65								
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60								
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57								
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53								
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50								

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	645381
5°	645916
10°	668651
15°	669766
20°	616630
25°	525395
30°	402209
35°	284159
40°	167733
45°	68096
50°	24681
55°	13753
60°	7889
65°	4343
70°	4568
75°	3546
80°	3712
85°	3134

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 68096 cd/sqm



TEST NUMBER: P754349

CATALOG NUMBER: LD4D80BD010-EU4DR6570959030-4LBSQW1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	568.8	9.5
10°-20°	1640.7	27.3
20°-30°	1968.5	32.8
30°-40°	1322.9	22.1
40°-50°	396.0	6.6
50°-60°	69.9	1.2
60°-70°	19.9	0.3
70°-80°	9.8	0.2
80°-90°	3.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4177.9	69.6
0°-40°	5500.8	91.7
0°-60°	5966.7	99.5
0°-90°	5999.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5999.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5907	
5°	5889	569
15°	5921	1641
25°	4358	1968
35°	2130	1323
45°	441	396
55°	72	70
65°	17	20
75°	8	10
85°	2	3
90°	0	



TEST NUMBER: P754349

CATALOG NUMBER: LD4D80BD010-EU4DR6570959030-4LBSQW1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	5906.8
2.5°	5932.0
5°	5889.2
7.5°	5978.2
10°	6026.8
12.5°	6015.1
15°	5921.1
17.5°	5691.1
20°	5303.3
22.5°	4846.7
25°	4358.1
27.5°	3806.7
30°	3188.0
32.5°	2627.3
35°	2130.4
37.5°	1639.3
40°	1176.0
42.5°	768.0
45°	440.7
47.5°	233.4
50°	145.2
52.5°	100.7
55°	72.2
57.5°	52.0
60°	36.1
62.5°	23.5
65°	16.8
67.5°	15.1
70°	14.3
72.5°	10.9
75°	8.4
77.5°	7.6
80°	5.9
82.5°	4.2
85°	2.5
87.5°	1.7
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)