

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P752789

Luminaire Tested: LD4D70BD010-EU4DR6570959030-4LBSQW1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P752789
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D70BD010-EU4DR6570959030-4LBSQW1MW
Description: 4 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5347.0 lumens
Efficiency: N/A
Efficacy: 80.3 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 66.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P752789
CATALOG NUMBER: LD4D70BD010-EU4DR6570959030-4LBSQW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P752789

CATALOG NUMBER: LD4D70BD010-EU4DR6570959030-4LBSQW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93		
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87		
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80		
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75		
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69		
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65		
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60		
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57		
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53		
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	575203
5°	575678
10°	595948
15°	596931
20°	549575
25°	468263
30°	358481
35°	253254
40°	149490
45°	60695
50°	21995
55°	12249
60°	7036
65°	3878
70°	4057
75°	3166
80°	3272
85°	2758

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 60695 cd/sqm



TEST NUMBER: P752789

CATALOG NUMBER: LD4D70BD010-EU4DR6570959030-4LBSQW1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	506.9	9.5
10°-20°	1462.3	27.3
20°-30°	1754.4	32.8
30°-40°	1179.0	22.1
40°-50°	352.9	6.6
50°-60°	62.3	1.2
60°-70°	17.7	0.3
70°-80°	8.7	0.2
80°-90°	2.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3723.6	69.6
0°-40°	4902.6	91.7
0°-60°	5317.9	99.5
0°-90°	5347.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5347.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5264	
5°	5249	507
15°	5277	1462
25°	3884	1754
35°	1899	1179
45°	393	353
55°	64	62
65°	15	18
75°	8	9
85°	2	3
90°	0	



TEST NUMBER: P752789

CATALOG NUMBER: LD4D70BD010-EU4DR6570959030-4LBSQW1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	5264.5
2.5°	5287.0
5°	5248.8
7.5°	5328.1
10°	5371.5
12.5°	5361.0
15°	5277.2
17.5°	5072.3
20°	4726.6
22.5°	4319.6
25°	3884.2
27.5°	3392.7
30°	2841.4
32.5°	2341.6
35°	1898.7
37.5°	1461.1
40°	1048.1
42.5°	684.5
45°	392.8
47.5°	208.0
50°	129.4
52.5°	89.8
55°	64.3
57.5°	46.4
60°	32.2
62.5°	20.9
65°	15.0
67.5°	13.5
70°	12.7
72.5°	9.7
75°	7.5
77.5°	6.7
80°	5.2
82.5°	3.7
85°	2.2
87.5°	1.5
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)