

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P754283

Luminaire Tested: LD4D80BD010-EU4DR6070959035-4LBSQW1B

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P754283  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D80BD010-EU4DR6070959035-4LBSQW1B  
Description: 4 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 60° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6154.4 lumens  
Efficiency: N/A  
Efficacy: 78.0 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 78.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P754283  
CATALOG NUMBER: LD4D80BD010-EU4DR6070959035-4LBSQW1B

### Luminous Intensity Polar Plot





TEST NUMBER: P754283  
 CATALOG NUMBER: LD4D80BD010-EU4DR6070959035-4LBSQW1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93	93	93	93
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86	86	86	86
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80	80	80	80
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75	75	75	75
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70	70	70	70
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66	66	66	66
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62	62	62	62
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59	59	59	59
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55	55	55	55
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53	53	53	53

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	798598
5°	818232
10°	828114
15°	788887
20°	695556
25°	562586
30°	380547
35°	190697
40°	30936
45°	30270
50°	30885
55°	31355
60°	32210
65°	32963
70°	33735
75°	34152
80°	32908
85°	27454

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 75°  
 Luminance: 34152 cd/sqm



TEST NUMBER: P754283

CATALOG NUMBER: LD4D80BD010-EU4DR6070959035-4LBSQW1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	713.0	11.6
10°-20°	1929.1	31.3
20°-30°	2075.6	33.7
30°-40°	902.2	14.7
40°-50°	151.5	2.5
50°-60°	147.3	2.4
60°-70°	126.0	2.0
70°-80°	84.3	1.4
80°-90°	25.2	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4717.7	76.7
0°-40°	5619.9	91.3
0°-60°	5918.8	96.2
0°-90°	6154.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6154.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	7309	
5°	7460	713
15°	6974	1929
25°	4667	2076
35°	1430	902
45°	196	152
55°	165	147
65°	128	126
75°	81	84
85°	22	25
90°	0	



TEST NUMBER: P754283

CATALOG NUMBER: LD4D80BD010-EU4DR6070959035-4LBSQW1B

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	7309.1
2.5°	7514.5
5°	7460.3
7.5°	7477.4
10°	7464.1
12.5°	7310.0
15°	6974.2
17.5°	6523.4
20°	5982.1
22.5°	5402.8
25°	4666.6
27.5°	3732.5
30°	3016.3
32.5°	2324.7
35°	1429.7
37.5°	611.6
40°	216.9
42.5°	199.8
45°	195.9
47.5°	189.3
50°	181.7
52.5°	173.1
55°	164.6
57.5°	156.0
60°	147.4
62.5°	137.9
65°	127.5
67.5°	117.0
70°	105.6
72.5°	93.2
75°	80.9
77.5°	66.6
80°	52.3
82.5°	37.1
85°	21.9
87.5°	7.6
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)