

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P754298

Luminaire Tested: LD4D80BD010-EU4DR6070959050-4LBCSSQMB

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P754298
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-60)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D80BD010-EU4DR6070959050-4LBCSSQMB
Description: 4 INCH SQAURE SHALLOW CAST MATTE BLACK TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7923.1 lumens
Efficiency: N/A
Efficacy: 100.4 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 78.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P754298
CATALOG NUMBER: LD4D80BD010-EU4DR6070959050-4LBCSSQMB

Luminous Intensity Polar Plot





TEST NUMBER: P754298

CATALOG NUMBER: LD4D80BD010-EU4DR6070959050-4LBCSSQMB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94				
2	108	103	99	96	106	101	98	95	98	95	92	95	93	90	92	90	89	87				
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81				
4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77	75				
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70				
6	87	79	73	68	86	78	72	68	76	71	68	75	70	67	74	70	67	65				
7	83	74	68	63	82	73	67	63	72	67	63	71	66	63	69	65	62	61				
8	79	69	63	59	78	69	63	59	68	63	59	67	62	59	66	61	58	57				
9	75	65	59	55	74	65	59	55	64	59	55	63	58	55	62	58	55	53				
10	72	62	56	52	71	61	56	52	61	55	52	60	55	52	59	55	52	50				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	866329
5°	864209
10°	892918
15°	893835
20°	822421
25°	699526
30°	533015
35°	376926
40°	221333
45°	89311
50°	29814
55°	14344
60°	5900
65°	879
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 89311 cd/sqm



TEST NUMBER: P754298

CATALOG NUMBER: LD4D80BD010-EU4DR6070959050-4LBCSSQMB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	760.1	9.6
10°-20°	2189.1	27.6
20°-30°	2620.1	33.1
30°-40°	1752.4	22.1
40°-50°	519.6	6.6
50°-60°	74.7	0.9
60°-70°	7.1	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5569.3	70.3
0°-40°	7321.8	92.4
0°-60°	7916.0	99.9
0°-90°	7923.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7923.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7929	
5°	7880	760
15°	7902	2189
25°	5802	2620
35°	2826	1752
45°	578	520
55°	75	75
65°	3	7
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P754298

CATALOG NUMBER: LD4D80BD010-EU4DR6070959050-4LBCSSQMB

CANDELA DISTRIBUTION (FULL):

	0°
0°	7929.0
2.5°	7918.9
5°	7879.5
7.5°	7986.4
10°	8048.2
12.5°	8037.0
15°	7902.0
17.5°	7583.8
20°	7073.2
22.5°	6460.4
25°	5802.5
27.5°	5061.5
30°	4224.8
32.5°	3478.1
35°	2825.9
37.5°	2172.6
40°	1551.8
42.5°	1023.3
45°	578.0
47.5°	295.7
50°	175.4
52.5°	113.6
55°	75.3
57.5°	48.4
60°	27.0
62.5°	11.2
65°	3.4
67.5°	1.1
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)