

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P754310

Luminaire Tested: LD4D80BD010-EU4DR6070959050-4LBSQW1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P754310
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D80BD010-EU4DR6070959050-4LBSQW1MW
Description: 4 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7308.7 lumens
Efficiency: N/A
Efficacy: 92.6 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 78.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P754310
CATALOG NUMBER: LD4D80BD010-EU4DR6070959050-4LBSQW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P754310

CATALOG NUMBER: LD4D80BD010-EU4DR6070959050-4LBSQW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66																			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62																			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	948372
5°	971693
10°	983428
15°	936853
20°	826014
25°	668109
30°	451917
35°	226457
40°	36741
45°	35956
50°	36682
55°	37222
60°	38263
65°	39142
70°	40060
75°	40527
80°	39074
85°	32594

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 40527 cd/sqm



TEST NUMBER: P754310

CATALOG NUMBER: LD4D80BD010-EU4DR6070959050-4LBSQW1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	846.7	11.6
10°-20°	2290.9	31.3
20°-30°	2464.9	33.7
30°-40°	1071.4	14.7
40°-50°	180.0	2.5
50°-60°	175.0	2.4
60°-70°	149.7	2.0
70°-80°	100.1	1.4
80°-90°	30.0	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5602.5	76.7
0°-40°	6674.0	91.3
0°-60°	7028.9	96.2
0°-90°	7308.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7308.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8680	
5°	8860	847
15°	8282	2291
25°	5542	2465
35°	1698	1071
45°	233	180
55°	195	175
65°	151	150
75°	96	100
85°	26	30
90°	0	



TEST NUMBER: P754310

CATALOG NUMBER: LD4D80BD010-EU4DR6070959050-4LBSQW1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	8679.9
2.5°	8923.9
5°	8859.5
7.5°	8879.9
10°	8864.0
12.5°	8681.0
15°	8282.3
17.5°	7746.9
20°	7104.1
22.5°	6416.2
25°	5541.9
27.5°	4432.6
30°	3582.0
32.5°	2760.8
35°	1697.8
37.5°	726.3
40°	257.6
42.5°	237.2
45°	232.7
47.5°	224.8
50°	215.8
52.5°	205.6
55°	195.4
57.5°	185.3
60°	175.1
62.5°	163.8
65°	151.4
67.5°	138.9
70°	125.4
72.5°	110.7
75°	96.0
77.5°	79.1
80°	62.1
82.5°	44.1
85°	26.0
87.5°	9.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)