

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P754557

Luminaire Tested: LD4D85BD010-EU4DR3070959024-4LBSQW1MW

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P754557
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D85BD010-EU4DR3070959024-4LBSQW1MW
Description: 4 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5699.8 lumens
Efficiency: N/A
Efficacy: 65.0 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')
CIE Type: Direct


Input Watts (W): 87.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P754557

CATALOG NUMBER: LD4D85BD010-EU4DR3070959024-4LBSQW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P754557

CATALOG NUMBER: LD4D85BD010-EU4DR3070959024-4LBSQW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																			
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																			
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89																			
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85																			
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82																			
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79																			
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77																			
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																			
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72																			
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1402864	1402864	1402864
5°	1362590	1361000	1362659
10°	1180211	1171887	1179931
15°	770025	765889	762046
20°	382899	397268	382386
25°	192881	217500	188929
30°	77222	84142	67287
35°	35816	34303	28752
40°	15468	17176	14568
45°	10911	13542	11009
50°	3751	9860	3965
55°	2162	4084	2282
60°	1516	1791	1516
65°	978	978	978
70°	604	403	604
75°	0	266	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
 Vertical Angle: 45°
 Luminance: 13542 cd/sqm



TEST NUMBER: P754557

CATALOG NUMBER: LD4D85BD010-EU4DR3070959024-4LBSQW1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1611.6	28.3
10°-20°	2595.6	45.5
20°-30°	1121.6	19.7
30°-40°	255.6	4.5
40°-50°	87.8	1.5
50°-60°	21.4	0.4
60°-70°	5.6	0.1
70°-80°	0.6	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5328.8	93.5
0°-40°	5584.5	98.0
0°-60°	5693.7	99.9
0°-90°	5699.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5699.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	18328	18328	18328	18328	18328	
5°	17734	17717	17713	17750	17735	1613
15°	9717	9600	9665	9634	9616	2602
25°	2284	2370	2575	2310	2237	1093
35°	383	391	367	364	308	260
45°	101	125	125	125	102	72
55°	16	17	31	18	17	16
65°	5	5	5	5	5	5
75°	0	0	1	0	0	1
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P754557

CATALOG NUMBER: LD4D85BD010-EU4DR3070959024-4LBSQW1MW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	18327.7	18327.7	18327.7	18327.7	18327.7
2.5°	18206.2	18193.6	18200.8	18209.8	18213.4
5°	17733.8	17716.7	17713.1	17750.0	17734.7
7.5°	16780.9	16756.6	16719.7	16803.4	16881.7
10°	15184.6	15157.6	15077.5	15117.1	15181.0
12.5°	12827.9	12740.6	12738.9	12864.8	12847.7
15°	9717.2	9600.3	9665.0	9633.5	9616.5
17.5°	6534.5	6489.6	6575.9	6549.8	6437.4
20°	4700.7	4712.4	4877.1	4794.3	4694.4
22.5°	3430.1	3472.4	3667.7	3454.4	3376.2
25°	2283.8	2370.1	2575.3	2309.9	2237.0
27.5°	1404.6	1444.2	1652.1	1386.6	1347.0
30°	873.7	853.9	952.0	817.0	761.3
32.5°	573.2	548.0	579.5	520.1	475.1
35°	383.3	391.4	367.1	364.4	307.7
37.5°	239.4	275.3	243.0	259.2	198.0
40°	154.8	199.8	171.9	189.9	145.8
42.5°	126.9	153.9	141.3	150.3	129.6
45°	100.8	125.1	125.1	125.1	101.7
47.5°	55.8	83.7	107.1	85.5	59.4
50°	31.5	42.3	82.8	44.1	33.3
52.5°	21.6	24.3	56.7	25.2	22.5
55°	16.2	17.1	30.6	18.0	17.1
57.5°	12.6	13.5	16.2	13.5	12.6
60°	9.9	9.9	11.7	10.8	9.9
62.5°	7.2	7.2	8.1	7.2	7.2
65°	5.4	5.4	5.4	5.4	5.4
67.5°	2.7	3.6	3.6	3.6	3.6
70°	2.7	1.8	1.8	1.8	2.7
72.5°	1.8	0.9	0.9	0.9	0.9
75°	0.0	0.0	0.9	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)