

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P753504

Luminaire Tested: LD4D75BD010-EU4DR6070959035-4LBSQW1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P753504
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D75BD010-EU4DR6070959035-4LBSQW1MW
Description: 4 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6530.7 lumens
Efficiency: N/A
Efficacy: 90.2 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 72.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P753504
CATALOG NUMBER: LD4D75BD010-EU4DR6070959035-4LBSQW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P753504

CATALOG NUMBER: LD4D75BD010-EU4DR6070959035-4LBSQW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66																			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62																			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	847415
5°	868256
10°	878739
15°	837119
20°	738089
25°	596981
30°	403811
35°	202355
40°	32819
45°	32124
50°	32772
55°	33260
60°	34199
65°	34980
70°	35779
75°	36221
80°	34921
85°	29084

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 36221 cd/sqm



TEST NUMBER: P753504

CATALOG NUMBER: LD4D75BD010-EU4DR6070959035-4LBSQW1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	756.6	11.6
10°-20°	2047.1	31.3
20°-30°	2202.5	33.7
30°-40°	957.4	14.7
40°-50°	160.8	2.5
50°-60°	156.3	2.4
60°-70°	133.8	2.0
70°-80°	89.5	1.4
80°-90°	26.8	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5006.1	76.7
0°-40°	5963.5	91.3
0°-60°	6280.6	96.2
0°-90°	6530.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6530.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7756	
5°	7916	757
15°	7401	2047
25°	4952	2202
35°	1517	957
45°	208	161
55°	175	156
65°	135	134
75°	86	89
85°	23	27
90°	0	



TEST NUMBER: P753504

CATALOG NUMBER: LD4D75BD010-EU4DR6070959035-4LBSQW1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	7755.9
2.5°	7973.9
5°	7916.4
7.5°	7934.6
10°	7920.4
12.5°	7756.9
15°	7400.6
17.5°	6922.2
20°	6347.9
22.5°	5733.2
25°	4951.9
27.5°	3960.7
30°	3200.7
32.5°	2466.9
35°	1517.1
37.5°	649.0
40°	230.1
42.5°	212.0
45°	207.9
47.5°	200.9
50°	192.8
52.5°	183.7
55°	174.6
57.5°	165.5
60°	156.5
62.5°	146.4
65°	135.3
67.5°	124.2
70°	112.0
72.5°	98.9
75°	85.8
77.5°	70.7
80°	55.5
82.5°	39.4
85°	23.2
87.5°	8.1
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)