

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P753517

Luminaire Tested: LD4D75BD010-EU4DR6070959040-4LBSQW1MW

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P753517  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D75BD010-EU4DR6070959040-4LBSQW1MW  
Description: 4 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 60° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6836.0 lumens  
Efficiency: N/A  
Efficacy: 94.4 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 72.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P753517  
CATALOG NUMBER: LD4D75BD010-EU4DR6070959040-4LBSQW1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P753517

CATALOG NUMBER: LD4D75BD010-EU4DR6070959040-4LBSQW1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66																			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62																			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	887033
5°	908848
10°	919822
15°	876257
20°	772587
25°	624889
30°	422685
35°	211812
40°	34360
45°	33623
50°	34302
55°	34822
60°	35794
65°	36608
70°	37472
75°	37909
80°	36557
85°	30463

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 75°  
 Luminance: 37909 cd/sqm



TEST NUMBER: P753517

CATALOG NUMBER: LD4D75BD010-EU4DR6070959040-4LBSQW1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	792.0	11.6
10°-20°	2142.8	31.3
20°-30°	2305.4	33.7
30°-40°	1002.1	14.7
40°-50°	168.3	2.5
50°-60°	163.7	2.4
60°-70°	140.0	2.0
70°-80°	93.7	1.4
80°-90°	28.0	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5240.2	76.7
0°-40°	6242.3	91.3
0°-60°	6574.3	96.2
0°-90°	6836.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6836.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	8118	
5°	8286	792
15°	7747	2143
25°	5183	2305
35°	1588	1002
45°	218	168
55°	183	164
65°	142	140
75°	90	94
85°	24	28
90°	0	



TEST NUMBER: P753517

CATALOG NUMBER: LD4D75BD010-EU4DR6070959040-4LBSQW1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	8118.5
2.5°	8346.7
5°	8286.5
7.5°	8305.5
10°	8290.7
12.5°	8119.6
15°	7746.6
17.5°	7245.8
20°	6644.6
22.5°	6001.2
25°	5183.4
27.5°	4145.9
30°	3350.3
32.5°	2582.2
35°	1588.0
37.5°	679.4
40°	240.9
42.5°	221.9
45°	217.6
47.5°	210.3
50°	201.8
52.5°	192.3
55°	182.8
57.5°	173.3
60°	163.8
62.5°	153.2
65°	141.6
67.5°	130.0
70°	117.3
72.5°	103.5
75°	89.8
77.5°	74.0
80°	58.1
82.5°	41.2
85°	24.3
87.5°	8.5
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)