

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P740850

Luminaire Tested: LD4D08D010-EU4DR150210IC9024-4LBCSSQMMS

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P740850
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-21)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D08D010-EU4DR150210IC9024-4LBCSSQMMS
Description: 4 INCH SQAURE SHALLOW CAST MATTE METALLIC SILVER TRIM, WITH 15° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 603.1 lumens
Efficiency: N/A
Efficacy: 67.8 lumens/watt
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.23
Luminous Opening: Vertical Cylinder (Dia: 0.35' x H: 0.35')
CIE Type: Direct

Input Watts (W): 8.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P740850
CATALOG NUMBER: LD4D08D010-EU4DR150210IC9024-4LBCSSQMMS

Luminous Intensity Polar Plot





TEST NUMBER: P740850

CATALOG NUMBER: LD4D08D010-EU4DR150210IC9024-4LBCSSQMMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98																			
2	113	110	107	105	111	108	106	104	105	103	102	102	101	100	100	99	98	96																			
3	110	106	103	101	108	105	102	100	103	100	99	100	99	97	98	97	96	94																			
4	108	103	100	98	106	102	99	97	100	98	96	99	97	95	97	95	94	93																			
5	106	101	98	95	104	100	97	95	99	96	94	97	95	93	96	94	92	92																			
6	104	99	95	93	102	98	95	93	97	94	92	96	93	92	95	93	91	90																			
7	102	97	94	91	101	96	93	91	95	93	91	94	92	90	93	91	90	89																			
8	100	95	92	90	99	95	92	90	94	91	89	93	91	89	92	90	89	88																			
9	99	93	90	88	98	93	90	88	92	90	88	92	89	88	91	89	88	87																			
10	97	92	89	87	96	92	89	87	91	89	87	91	88	87	90	88	86	86																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	924599	924599	924599
5°	543339	536306	540544
10°	162159	163298	165798
15°	40336	41118	39850
20°	12069	13975	12323
25°	4253	5422	4308
30°	1565	2059	1587
35°	784	886	755
40°	497	547	497
45°	364	392	364
50°	292	292	292
55°	244	244	244
60°	197	197	197
65°	150	150	150
70°	124	124	124
75°	76	76	106
80°	55	55	55
85°	25	25	25

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 392 cd/sqm



TEST NUMBER: P740850

CATALOG NUMBER: LD4D08D010-EU4DR150210IC9024-4LBCSSQMMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	391.2	64.9
10°-20°	160.9	26.7
20°-30°	32.0	5.3
30°-40°	8.0	1.3
40°-50°	4.2	0.7
50°-60°	3.1	0.5
60°-70°	2.2	0.4
70°-80°	1.2	0.2
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	584.0	96.8
0°-40°	592.0	98.2
0°-60°	599.3	99.4
0°-90°	603.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	603.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	8217	8217	8217	8217	8217	
5°	5346	5291	5277	5314	5319	390
15°	464	473	473	465	459	159
25°	55	62	70	62	55	29
35°	11	12	12	12	10	7
45°	5	5	6	5	5	4
55°	4	4	4	4	4	3
65°	2	2	2	2	2	2
75°	1	1	1	1	1	1
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P740850

CATALOG NUMBER: LD4D08D010-EU4DR150210IC9024-4LBCSSQMMS

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	8217.2	8217.2	8217.2	8217.2	8217.2
2.5°	7412.3	7418.5	7421.0	7428.3	7455.4
5°	5346.3	5291.4	5277.1	5313.6	5318.8
7.5°	3166.9	3178.1	3218.8	3227.8	3195.1
10°	1737.9	1752.2	1750.1	1762.6	1776.9
12.5°	888.8	877.7	874.2	888.4	868.6
15°	464.4	473.1	473.4	465.1	458.8
17.5°	249.8	259.9	276.6	263.0	242.1
20°	147.5	156.5	170.8	159.7	150.6
22.5°	91.1	98.4	108.5	99.8	92.5
25°	54.6	61.9	69.6	61.6	55.3
27.5°	32.4	38.6	43.5	38.3	32.0
30°	20.9	24.4	27.5	24.0	21.2
32.5°	14.6	16.0	17.4	16.0	14.6
35°	10.8	11.5	12.2	11.5	10.4
37.5°	8.3	9.0	9.4	8.7	8.0
40°	7.0	7.3	7.7	7.3	7.0
42.5°	5.9	6.3	6.3	6.3	5.9
45°	5.2	5.2	5.6	5.2	5.2
47.5°	4.5	4.5	4.9	4.5	4.5
50°	4.2	4.2	4.2	4.2	4.2
52.5°	3.8	3.8	3.8	3.8	3.8
55°	3.5	3.5	3.5	3.5	3.5
57.5°	3.1	3.1	3.1	3.1	3.1
60°	2.8	2.8	2.8	2.8	2.8
62.5°	2.4	2.4	2.4	2.4	2.4
65°	2.1	2.1	2.1	2.1	2.1
67.5°	2.1	2.1	2.1	2.1	2.1
70°	1.7	1.7	1.7	1.7	1.7
72.5°	1.4	1.4	1.4	1.4	1.4
75°	1.0	1.0	1.0	1.0	1.4
77.5°	1.0	1.0	1.0	1.0	1.0
80°	0.7	0.7	0.7	0.7	0.7
82.5°	0.7	0.7	0.7	0.7	0.7
85°	0.3	0.3	0.3	0.3	0.3
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)