

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P755158

Luminaire Tested: LD4D85BD010-EU4DR6570959050-4LBCSSQMW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P755158
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D85BD010-EU4DR6570959050-4LBCSSQMW
Description: 4 INCH SQAURE SHALLOW CAST MATTE WHITE TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7737.0 lumens
Efficiency: N/A
Efficacy: 88.2 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 87.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P755158
CATALOG NUMBER: LD4D85BD010-EU4DR6570959050-4LBCSSQMW

Luminous Intensity Polar Plot





TEST NUMBER: P755158

CATALOG NUMBER: LD4D85BD010-EU4DR6570959050-4LBCSSQMW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93																			
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85																			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78																			
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72																			
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66																			
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61																			
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56																			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52																			
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49																			
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	410281
5°	409246
10°	408901
15°	396294
20°	360774
25°	314391
30°	261488
35°	207192
40°	149539
45°	94473
50°	49246
55°	26169
60°	13748
65°	7559
70°	3176
75°	3498
80°	2422
85°	2077

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 94473 cd/sqm



TEST NUMBER: P755158

CATALOG NUMBER: LD4D85BD010-EU4DR6570959050-4LBCSSQMW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	664.3	8.6
10°-20°	1819.2	23.5
20°-30°	2223.7	28.7
30°-40°	1804.2	23.3
40°-50°	899.1	11.6
50°-60°	250.8	3.2
60°-70°	57.0	0.7
70°-80°	14.8	0.2
80°-90°	3.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4707.2	60.8
0°-40°	6511.5	84.2
0°-60°	7661.3	99.0
0°-90°	7737.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7737.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7025	
5°	6980	664
15°	6554	1819
25°	4879	2224
35°	2906	1804
45°	1144	899
55°	257	251
65°	55	57
75°	16	15
85°	3	4
90°	0	



TEST NUMBER: P755158

CATALOG NUMBER: LD4D85BD010-EU4DR6570959050-4LBCSSQMW

CANDELA DISTRIBUTION (FULL):

	0°
0°	7024.9
2.5°	7019.8
5°	6980.5
7.5°	6957.8
10°	6894.9
12.5°	6766.8
15°	6554.2
17.5°	6221.8
20°	5804.7
22.5°	5354.6
25°	4878.7
27.5°	4369.8
30°	3877.4
32.5°	3391.2
35°	2906.0
37.5°	2421.8
40°	1961.4
42.5°	1529.9
45°	1143.8
47.5°	797.0
50°	542.0
52.5°	373.7
55°	257.0
57.5°	173.4
60°	117.7
62.5°	81.6
65°	54.7
67.5°	27.9
70°	18.6
72.5°	17.5
75°	15.5
77.5°	10.3
80°	7.2
82.5°	5.2
85°	3.1
87.5°	2.1
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)