

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P755882

Luminaire Tested: LD4D90BD010-EU4DR6570959024-4LBSQW1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P755882
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D90BD010-EU4DR6570959024-4LBSQW1B
Description: 4 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4938.4 lumens
Efficiency: N/A
Efficacy: 49.9 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 98.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P755882
CATALOG NUMBER: LD4D90BD010-EU4DR6570959024-4LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P755882

CATALOG NUMBER: LD4D90BD010-EU4DR6570959024-4LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80			
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75			
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69			
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65			
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57			
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53			
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	531259
5°	531698
10°	550416
15°	551323
20°	507589
25°	432494
30°	331091
35°	233913
40°	138066
45°	56059
50°	20313
55°	11315
60°	6490
65°	3568
70°	3738
75°	2913
80°	3020
85°	2633

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 56059 cd/sqm



TEST NUMBER: P755882

CATALOG NUMBER: LD4D90BD010-EU4DR6570959024-4LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	468.2	9.5
10°-20°	1350.5	27.3
20°-30°	1620.4	32.8
30°-40°	1088.9	22.1
40°-50°	326.0	6.6
50°-60°	57.5	1.2
60°-70°	16.3	0.3
70°-80°	8.0	0.2
80°-90°	2.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3439.1	69.6
0°-40°	4528.1	91.7
0°-60°	4911.6	99.5
0°-90°	4938.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4938.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4862	
5°	4848	468
15°	4874	1351
25°	3588	1620
35°	1754	1089
45°	363	326
55°	59	58
65°	14	16
75°	7	8
85°	2	3
90°	0	



TEST NUMBER: P755882

CATALOG NUMBER: LD4D90BD010-EU4DR6570959024-4LBSQW1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	4862.3
2.5°	4883.0
5°	4847.8
7.5°	4921.0
10°	4961.1
12.5°	4951.4
15°	4874.0
17.5°	4684.7
20°	4365.5
22.5°	3989.6
25°	3587.5
27.5°	3133.5
30°	2624.3
32.5°	2162.7
35°	1753.7
37.5°	1349.4
40°	968.0
42.5°	632.2
45°	362.8
47.5°	192.1
50°	119.5
52.5°	82.9
55°	59.4
57.5°	42.8
60°	29.7
62.5°	19.3
65°	13.8
67.5°	12.4
70°	11.7
72.5°	9.0
75°	6.9
77.5°	6.2
80°	4.8
82.5°	3.5
85°	2.1
87.5°	1.4
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)