

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P741202

Luminaire Tested: LD4D08D010-EU4DR350210IC9035-4LBCSSQMW

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P741202
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D08D010-EU4DR350210IC9035-4LBCSSQMW
Description: 4 INCH SQAURE SHALLOW CAST MATTE WHITE TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 737.6 lumens
Efficiency: N/A
Efficacy: 82.9 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 8.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P741202
CATALOG NUMBER: LD4D08D010-EU4DR350210IC9035-4LBCSSQMW

Luminous Intensity Polar Plot





TEST NUMBER: P741202

CATALOG NUMBER: LD4D08D010-EU4DR350210IC9035-4LBCSSQMW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																		
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																			
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	98	96																												
2	110	106	103	101	108	105	102	99	102	99	97	99	97	95	96	95	93	92																												
3	106	101	97	94	105	100	96	93	97	95	92	95	93	91	93	91	89	88																												
4	103	97	92	89	101	96	92	89	94	90	88	92	89	87	90	88	86	84																												
5	99	93	88	85	98	92	87	84	90	86	84	89	85	83	87	84	82	81																												
6	96	89	84	81	94	88	84	81	87	83	80	85	82	80	84	81	79	78																												
7	93	85	81	78	91	85	80	77	84	80	77	83	79	77	82	79	76	75																												
8	90	82	78	74	88	82	77	74	81	77	74	80	76	74	79	76	73	72																												
9	87	79	75	72	86	79	75	72	78	74	71	77	74	71	77	73	71	70																												
10	84	77	72	69	83	76	72	69	76	72	69	75	71	69	74	71	69	68																												

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	221756
5°	216537
10°	195166
15°	151484
20°	85914
25°	33430
30°	12465
35°	6829
40°	4464
45°	2720
50°	1734
55°	1219
60°	896
65°	491
70°	32
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2720 cd/sqm



TEST NUMBER: P741202

CATALOG NUMBER: LD4D08D010-EU4DR350210IC9035-4LBCSSQMW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	181.6	24.6
10°-20°	354.5	48.1
20°-30°	144.6	19.6
30°-40°	34.6	4.7
40°-50°	14.4	2.0
50°-60°	6.0	0.8
60°-70°	1.9	0.3
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	680.7	92.3
0°-40°	715.3	97.0
0°-60°	735.7	99.7
0°-90°	737.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	737.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2030	
5°	1974	182
15°	1339	355
25°	277	145
35°	51	35
45°	18	14
55°	6	6
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P741202

CATALOG NUMBER: LD4D08D010-EU4DR350210IC9035-4LBCSSQMW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2029.6
2.5°	2017.4
5°	1974.3
7.5°	1888.4
10°	1759.1
12.5°	1576.9
15°	1339.2
17.5°	1048.4
20°	738.9
22.5°	471.2
25°	277.3
27.5°	156.7
30°	98.8
32.5°	69.4
35°	51.2
37.5°	39.6
40°	31.3
42.5°	24.1
45°	17.6
47.5°	13.2
50°	10.2
52.5°	8.1
55°	6.4
57.5°	5.2
60°	4.1
62.5°	3.0
65°	1.9
67.5°	0.7
70°	0.1
72.5°	0.1
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.1
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)