

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P740901

Luminaire Tested: LD4D08D010-EU4DR150210IC9040-4LBCSSQMB

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P740901
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-21)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D08D010-EU4DR150210IC9040-4LBCSSQMB
Description: 4 INCH SQAURE SHALLOW CAST MATTE BLACK TRIM, WITH 15° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 750.0 lumens
Efficiency: N/A
Efficacy: 84.3 lumens/watt
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.23
Luminous Opening: Vertical Cylinder (Dia: 0.35' x H: 0.35')
CIE Type: Direct

Input Watts (W): 8.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P740901

CATALOG NUMBER: LD4D08D010-EU4DR150210IC9040-4LBCSSQMB

Luminous Intensity Polar Plot





TEST NUMBER: P740901

CATALOG NUMBER: LD4D08D010-EU4DR150210IC9040-4LBCSSQMB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98						98													
2	113	110	107	105	111	108	106	104	105	103	102	102	101	100	100	98	98	96						96													
3	110	106	103	101	108	105	102	100	103	100	99	100	99	97	98	97	96	94						94													
4	108	103	100	98	106	102	99	97	100	98	96	99	97	95	97	95	94	93						93													
5	106	101	98	95	104	100	97	95	98	96	94	97	95	93	96	94	92	92						92													
6	104	99	95	93	102	98	95	93	97	94	92	96	93	92	95	93	91	90						90													
7	102	97	94	91	101	96	93	91	95	93	91	94	92	90	93	91	90	89						89													
8	100	95	92	90	99	95	92	90	94	91	89	93	91	89	92	90	89	88						88													
9	99	93	90	88	98	93	90	88	92	90	88	92	89	88	91	89	87	87						87													
10	97	92	89	87	96	92	89	87	91	89	87	91	88	87	90	88	86	86						86													

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1149740	1149740	1149740
5°	675639	666889	672163
10°	201647	203056	206163
15°	50160	51133	49561
20°	15006	17379	15325
25°	5289	6738	5360
30°	1947	2561	1977
35°	973	1097	944
40°	618	675	618
45°	455	483	455
50°	362	362	362
55°	299	299	299
60°	246	246	246
65°	186	186	186
70°	161	161	161
75°	98	98	128
80°	71	71	71
85°	33	33	33

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 483 cd/sqm



TEST NUMBER: P740901

CATALOG NUMBER: LD4D08D010-EU4DR150210IC9040-4LBCSSQMB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	486.4	64.9
10°-20°	200.1	26.7
20°-30°	39.7	5.3
30°-40°	9.9	1.3
40°-50°	5.2	0.7
50°-60°	3.9	0.5
60°-70°	2.7	0.4
70°-80°	1.6	0.2
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	726.2	96.8
0°-40°	736.1	98.2
0°-60°	745.2	99.4
0°-90°	750.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	750.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	10218	10218	10218	10218	10218	
5°	6648	6580	6562	6607	6614	485
15°	578	588	589	578	571	198
25°	68	77	86	77	69	36
35°	13	14	15	14	13	9
45°	6	6	7	6	6	5
55°	4	4	4	4	4	4
65°	3	3	3	3	3	3
75°	1	1	1	1	2	2
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P740901

CATALOG NUMBER: LD4D08D010-EU4DR150210IC9040-4LBCSSQMB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	10218.1	10218.1	10218.1	10218.1	10218.1
2.5°	9217.1	9224.9	9227.9	9237.0	9270.8
5°	6648.1	6579.8	6562.0	6607.4	6613.9
7.5°	3938.1	3951.9	4002.5	4013.8	3973.1
10°	2161.1	2178.8	2176.2	2191.8	2209.5
12.5°	1105.2	1091.4	1087.0	1104.8	1080.1
15°	577.5	588.3	588.7	578.3	570.6
17.5°	310.6	323.1	343.9	327.0	301.1
20°	183.4	194.7	212.4	198.5	187.3
22.5°	113.3	122.4	135.0	124.1	115.1
25°	67.9	77.0	86.5	76.6	68.8
27.5°	40.2	48.0	54.1	47.6	39.8
30°	26.0	30.3	34.2	29.8	26.4
32.5°	18.2	19.9	21.6	19.9	18.2
35°	13.4	14.3	15.1	14.3	13.0
37.5°	10.4	11.2	11.7	10.8	9.9
40°	8.7	9.1	9.5	9.1	8.7
42.5°	7.4	7.8	7.8	7.8	7.4
45°	6.5	6.5	6.9	6.5	6.5
47.5°	5.6	5.6	6.1	5.6	5.6
50°	5.2	5.2	5.2	5.2	5.2
52.5°	4.8	4.8	4.8	4.8	4.8
55°	4.3	4.3	4.3	4.3	4.3
57.5°	3.9	3.9	3.9	3.9	3.9
60°	3.5	3.5	3.5	3.5	3.5
62.5°	3.0	3.0	3.0	3.0	3.0
65°	2.6	2.6	2.6	2.6	2.6
67.5°	2.6	2.6	2.6	2.6	2.6
70°	2.2	2.2	2.2	2.2	2.2
72.5°	1.7	1.7	1.7	1.7	1.7
75°	1.3	1.3	1.3	1.3	1.7
77.5°	1.3	1.3	1.3	1.3	1.3
80°	0.9	0.9	0.9	0.9	0.9
82.5°	0.9	0.9	0.9	0.9	0.9
85°	0.4	0.4	0.4	0.4	0.4
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)