

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P740991

Luminaire Tested: LD4D08D010-EU4DR200210IC9040-4LBSQW1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P740991
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D08D010-EU4DR200210IC9040-4LBSQW1MW
Description: 4 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 20° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 742.7 lumens
Efficiency: N/A
Efficacy: 83.4 lumens/watt
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 8.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P740991

CATALOG NUMBER: LD4D08D010-EU4DR200210IC9040-4LBSQW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P740991

CATALOG NUMBER: LD4D08D010-EU4DR200210IC9040-4LBSQW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100														
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	98	96	95	94	94														
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	94	94	92	91	91	91														
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	93	92	91	91	89	88	88	88														
4	105	99	96	93	103	98	95	92	96	93	91	95	92	90	93	91	89	88	88	86	85	85	85														
5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	86	85	85	83	83	83	83														
6	99	93	89	86	98	92	88	86	91	87	85	90	87	84	88	86	84	83	83	81	81	81	81														
7	96	90	86	83	95	89	86	83	88	85	82	87	84	82	86	84	82	81	81	79	79	79	79														
8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	79	79	77	77	77	77														
9	91	85	81	78	91	85	81	78	84	80	78	83	80	78	82	80	78	77	77	75	75	75	75														
10	89	83	79	76	88	82	79	76	82	78	76	81	78	76	81	78	76	75	75	73	73	73	73														

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	461856
5°	416678
10°	233864
15°	118873
20°	50335
25°	23231
30°	12301
35°	6629
40°	3537
45°	2101
50°	1224
55°	648
60°	415
65°	284
70°	128
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2101 cd/sqm



TEST NUMBER: P740991

CATALOG NUMBER: LD4D08D010-EU4DR200210IC9040-4LBSQW1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	301.0	40.5
10°-20°	296.3	39.9
20°-30°	96.8	13.0
30°-40°	33.0	4.4
40°-50°	11.1	1.5
50°-60°	3.3	0.4
60°-70°	1.1	0.2
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	694.1	93.5
0°-40°	727.1	97.9
0°-60°	741.5	99.8
0°-90°	742.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	742.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4227	
5°	3799	301
15°	1051	296
25°	193	97
35°	50	33
45°	14	11
55°	3	3
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P740991

CATALOG NUMBER: LD4D08D010-EU4DR200210IC9040-4LBSQW1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	4227.1
0.5°	4227.1
1°	4221.8
1.5°	4211.3
2°	4192.1
2.5°	4166.5
3°	4130.4
3.5°	4079.9
4°	4005.0
4.5°	3913.9
5°	3799.1
5.5°	3648.2
6°	3493.5
6.5°	3316.2
7°	3142.6
7.5°	2939.4
8°	2758.0
8.5°	2575.4
9°	2406.8
9.5°	2252.1
10°	2107.9
12.5°	1513.5
15°	1050.9
17.5°	686.6
20°	432.9
22.5°	280.4
25°	192.7
27.5°	135.5
30°	97.5
32.5°	70.0
35°	49.7
37.5°	34.6
40°	24.8
42.5°	18.1
45°	13.6
47.5°	10.5
50°	7.2
52.5°	4.5
55°	3.4
57.5°	2.6
60°	1.9
62.5°	1.5
65°	1.1



TEST NUMBER: P740991

CATALOG NUMBER: LD4D08D010-EU4DR200210IC9040-4LBSQW1MW

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





67.5°		0.8
70°		0.4

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)