

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P741472

Luminaire Tested: LD4D08D010-EU4DR500210IC9050-4LBSQW1MW

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P741472
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-44)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D08D010-EU4DR500210IC9050-4LBSQW1MW
Description: 4 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 50° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 769.2 lumens
Efficiency: N/A
Efficacy: 86.4 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.73
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 8.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P741472

CATALOG NUMBER: LD4D08D010-EU4DR500210IC9050-4LBSQW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P741472
 CATALOG NUMBER: LD4D08D010-EU4DR500210IC9050-4LBSQW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																		
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																			
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	114	112	109	107	112	110	108	106	106	104	102	102	101	99	98	97	97	95	95	93	91	88	86	85	85	83	82	80																		
2	109	105	101	98	107	103	100	97	100	98	95	97	95	93	95	93	91	88	86	85	85	83	82	80	77	76	74	72																		
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	85	85	83	82	80	77	76	74	72	70	69																		
4	100	94	89	85	99	93	88	85	90	87	84	89	85	83	87	84	82	80	77	76	74	72	70	69	67	65	63	62																		
5	96	89	84	80	95	88	83	79	86	82	79	85	81	78	83	80	77	76	74	72	70	69	67	65	63	62	60	59																		
6	92	84	79	75	91	83	79	75	82	78	74	81	77	74	79	76	74	72	70	69	67	65	63	62	60	59	57	56																		
7	88	80	75	71	87	79	74	71	78	74	71	77	73	70	76	73	70	69	67	65	63	62	60	59	57	56	54	53																		
8	85	76	71	67	84	76	71	67	75	70	67	74	70	67	73	69	66	65	63	62	60	59	57	56	54	53	51	50																		
9	81	73	68	64	80	72	67	64	71	67	64	71	67	64	70	66	63	62	60	59	57	56	54	53	51	50	48	47																		
10	78	70	64	61	77	69	64	61	68	64	61	68	64	61	67	63	60	59	57	56	54	53	51	50	48	47	45	44																		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	135418
5°	134005
10°	131793
15°	120004
20°	99867
25°	70887
30°	37521
35°	15286
40°	5677
45°	2596
50°	1054
55°	552
60°	284
65°	78
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2596 cd/sqm



TEST NUMBER: P741472

CATALOG NUMBER: LD4D08D010-EU4DR500210IC9050-4LBSQW1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	115.5	15.0
10°-20°	291.8	37.9
20°-30°	262.2	34.1
30°-40°	82.1	10.7
40°-50°	14.4	1.9
50°-60°	2.9	0.4
60°-70°	0.4	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	669.5	87.0
0°-40°	751.5	97.7
0°-60°	768.8	99.9
0°-90°	769.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	769.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1239	
5°	1222	115
15°	1061	292
25°	588	262
35°	115	82
45°	17	14
55°	3	3
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P741472

CATALOG NUMBER: LD4D08D010-EU4DR500210IC9050-4LBSQW1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1239.4
2.5°	1233.2
5°	1221.8
7.5°	1204.2
10°	1187.9
12.5°	1135.6
15°	1060.9
17.5°	966.1
20°	858.9
22.5°	734.8
25°	588.0
27.5°	432.3
30°	297.4
32.5°	193.6
35°	114.6
37.5°	65.8
40°	39.8
42.5°	25.9
45°	16.8
47.5°	10.3
50°	6.2
52.5°	4.3
55°	2.9
57.5°	2.0
60°	1.3
62.5°	0.7
65°	0.3
67.5°	0.1
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)