

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P756585

Luminaire Tested: LD4D95BD010-EU4DR6070959024-4LBSQW1MW

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P756585  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D95BD010-EU4DR6070959024-4LBSQW1MW  
Description: 4 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 60° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6800.2 lumens  
Efficiency: N/A  
Efficacy: 68.6 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 99.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P756585  
CATALOG NUMBER: LD4D95BD010-EU4DR6070959024-4LBSQW1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P756585

CATALOG NUMBER: LD4D95BD010-EU4DR6070959024-4LBSQW1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66																			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62																			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	882390
5°	904088
10°	915018
15°	871676
20°	768552
25°	621622
30°	420478
35°	210705
40°	34174
45°	33453
50°	34115
55°	34631
60°	35597
65°	36401
70°	37281
75°	37698
80°	36368
85°	30338

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 75°  
 Luminance: 37698 cd/sqm



TEST NUMBER: P756585

CATALOG NUMBER: LD4D95BD010-EU4DR6070959024-4LBSQW1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	787.8	11.6
10°-20°	2131.5	31.3
20°-30°	2293.4	33.7
30°-40°	996.9	14.7
40°-50°	167.4	2.5
50°-60°	162.8	2.4
60°-70°	139.2	2.0
70°-80°	93.2	1.4
80°-90°	27.9	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5212.8	76.7
0°-40°	6209.6	91.3
0°-60°	6539.9	96.2
0°-90°	6800.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6800.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	8076	
5°	8243	788
15°	7706	2132
25°	5156	2293
35°	1580	997
45°	216	167
55°	182	163
65°	141	139
75°	89	93
85°	24	28
90°	0	



TEST NUMBER: P756585

CATALOG NUMBER: LD4D95BD010-EU4DR6070959024-4LBSQW1MW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	8076.0
2.5°	8303.1
5°	8243.1
7.5°	8262.1
10°	8247.4
12.5°	8077.1
15°	7706.1
17.5°	7207.9
20°	6609.9
22.5°	5969.8
25°	5156.3
27.5°	4124.2
30°	3332.8
32.5°	2568.7
35°	1579.7
37.5°	675.8
40°	239.6
42.5°	220.7
45°	216.5
47.5°	209.2
50°	200.7
52.5°	191.3
55°	181.8
57.5°	172.4
60°	162.9
62.5°	152.4
65°	140.8
67.5°	129.3
70°	116.7
72.5°	103.0
75°	89.3
77.5°	73.6
80°	57.8
82.5°	41.0
85°	24.2
87.5°	8.4
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)