

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P754233

Luminaire Tested: LD4D80BD010-EU4DR6070959024-4LBCSSQMB

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P754233
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-60)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D80BD010-EU4DR6070959024-4LBCSSQMB
Description: 4 INCH SQAURE SHALLOW CAST MATTE BLACK TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6372.9 lumens
Efficiency: N/A
Efficacy: 80.8 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 78.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P754233
CATALOG NUMBER: LD4D80BD010-EU4DR6070959024-4LBCSSQMB

Luminous Intensity Polar Plot





TEST NUMBER: P754233

CATALOG NUMBER: LD4D80BD010-EU4DR6070959024-4LBCSSQMB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94																																				
2	108	103	99	96	106	101	98	95	98	95	92	95	93	90	92	90	89	87																																				
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81																																				
4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77	75																																				
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70																																				
6	87	79	73	68	86	78	72	68	76	71	68	75	70	67	74	70	67	65																																				
7	83	74	68	63	82	73	67	63	72	67	63	71	66	63	69	65	62	61																																				
8	79	69	63	59	78	69	63	59	68	63	59	67	62	59	66	61	58	57																																				
9	75	65	59	55	74	65	59	55	64	59	55	63	58	55	62	58	55	53																																				
10	72	62	56	52	71	61	56	52	61	55	52	60	55	52	59	55	52	50																																				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	696821
5°	695118
10°	718211
15°	718948
20°	661511
25°	562659
30°	428729
35°	303179
40°	178030
45°	71835
50°	23984
55°	11544
60°	4742
65°	698
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 71835 cd/sqm



TEST NUMBER: P754233

CATALOG NUMBER: LD4D80BD010-EU4DR6070959024-4LBCSSQMB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	611.4	9.6
10°-20°	1760.8	27.6
20°-30°	2107.5	33.1
30°-40°	1409.6	22.1
40°-50°	417.9	6.6
50°-60°	60.1	0.9
60°-70°	5.7	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4479.6	70.3
0°-40°	5889.2	92.4
0°-60°	6367.2	99.9
0°-90°	6372.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6372.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6378	
5°	6338	611
15°	6356	1761
25°	4667	2107
35°	2273	1410
45°	465	418
55°	61	60
65°	3	6
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P754233

CATALOG NUMBER: LD4D80BD010-EU4DR6070959024-4LBCSSQMB

CANDELA DISTRIBUTION (FULL):

	0°
0°	6377.6
2.5°	6369.5
5°	6337.8
7.5°	6423.7
10°	6473.5
12.5°	6464.4
15°	6355.9
17.5°	6099.9
20°	5689.3
22.5°	5196.3
25°	4667.2
27.5°	4071.1
30°	3398.2
32.5°	2797.6
35°	2273.0
37.5°	1747.5
40°	1248.2
42.5°	823.1
45°	464.9
47.5°	237.9
50°	141.1
52.5°	91.4
55°	60.6
57.5°	38.9
60°	21.7
62.5°	9.0
65°	2.7
67.5°	0.9
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)