

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P754401

Luminaire Tested: LD4D80BD010-EU4DR7070959024-4LBSQW1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P754401
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D80BD010-EU4DR7070959024-4LBSQW1MW
Description: 4 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5415.4 lumens
Efficiency: N/A
Efficacy: 68.6 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 78.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P754401
CATALOG NUMBER: LD4D80BD010-EU4DR7070959024-4LBSQW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P754401

CATALOG NUMBER: LD4D80BD010-EU4DR7070959024-4LBSQW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10		0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	665234
5°	645467
10°	627479
15°	619237
20°	578248
25°	434411
30°	307082
35°	108774
40°	57195
45°	60926
50°	63079
55°	64271
60°	64661
65°	63315
70°	59738
75°	55344
80°	49141
85°	39865

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 64686 cd/sqm



TEST NUMBER: P754401

CATALOG NUMBER: LD4D80BD010-EU4DR7070959024-4LBSQW1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	555.1	10.3
10°-20°	1522.6	28.1
20°-30°	1676.9	31.0
30°-40°	640.7	11.8
40°-50°	302.5	5.6
50°-60°	300.7	5.6
60°-70°	240.8	4.4
70°-80°	138.4	2.6
80°-90°	37.6	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3754.6	69.3
0°-40°	4395.3	81.2
0°-60°	4998.6	92.3
0°-90°	5415.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5415.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6088	
5°	5885	555
15°	5474	1523
25°	3603	1677
35°	816	641
45°	394	303
55°	337	301
65°	245	241
75°	131	138
85°	32	38
90°	0	



TEST NUMBER: P754401

CATALOG NUMBER: LD4D80BD010-EU4DR7070959024-4LBSQW1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	6088.5
2.5°	6024.9
5°	5885.1
7.5°	5768.5
10°	5655.7
12.5°	5560.2
15°	5474.4
17.5°	5267.2
20°	4973.2
22.5°	4338.9
25°	3603.4
27.5°	3136.8
30°	2434.0
32.5°	1572.3
35°	815.5
37.5°	440.5
40°	401.0
42.5°	398.1
45°	394.3
47.5°	385.6
50°	371.1
52.5°	354.7
55°	337.4
57.5°	318.1
60°	295.9
62.5°	270.9
65°	244.9
67.5°	215.9
70°	187.0
72.5°	158.1
75°	131.1
77.5°	103.1
80°	78.1
82.5°	54.9
85°	31.8
87.5°	12.5
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)