

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P756690

Luminaire Tested: LD4D95BD010-EU4DR6570959035-4LBCSSQMB

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P756690
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D95BD010-EU4DR6570959035-4LBCSSQMB
Description: 4 INCH SQAURE SHALLOW CAST MATTE BLACK TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7828.4 lumens
Efficiency: N/A
Efficacy: 78.9 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P756690
CATALOG NUMBER: LD4D95BD010-EU4DR6570959035-4LBCSSQMB

Luminous Intensity Polar Plot





TEST NUMBER: P756690

CATALOG NUMBER: LD4D95BD010-EU4DR6570959035-4LBCSSQMB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93			93																
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85			85																
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78			78																
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72			72																
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66			66																
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61			61																
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56			56																
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52			52																
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49			49																
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46			46																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	415135
5°	414082
10°	413734
15°	400980
20°	365038
25°	318109
30°	264577
35°	209637
40°	151308
45°	95588
50°	49828
55°	26484
60°	13912
65°	7656
70°	3210
75°	3543
80°	2455
85°	2077

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 95588 cd/sqm



TEST NUMBER: P756690

CATALOG NUMBER: LD4D95BD010-EU4DR6570959035-4LBCSSQMB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	672.2	8.6
10°-20°	1840.7	23.5
20°-30°	2250.0	28.7
30°-40°	1825.6	23.3
40°-50°	909.7	11.6
50°-60°	253.7	3.2
60°-70°	57.7	0.7
70°-80°	15.0	0.2
80°-90°	3.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4762.9	60.8
0°-40°	6588.4	84.2
0°-60°	7751.9	99.0
0°-90°	7828.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7828.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7108	
5°	7063	672
15°	6632	1841
25°	4936	2250
35°	2940	1826
45°	1157	910
55°	260	254
65°	55	58
75°	16	15
85°	3	4
90°	0	



TEST NUMBER: P756690

CATALOG NUMBER: LD4D95BD010-EU4DR6570959035-4LBCSSQMB

CANDELA DISTRIBUTION (FULL):

0°	
0°	7108.0
2.5°	7102.7
5°	7063.0
7.5°	7040.1
10°	6976.4
12.5°	6846.8
15°	6631.7
17.5°	6295.3
20°	5873.3
22.5°	5417.9
25°	4936.4
27.5°	4421.5
30°	3923.2
32.5°	3431.3
35°	2940.3
37.5°	2450.4
40°	1984.6
42.5°	1548.0
45°	1157.3
47.5°	806.4
50°	548.4
52.5°	378.1
55°	260.1
57.5°	175.5
60°	119.1
62.5°	82.5
65°	55.4
67.5°	28.2
70°	18.8
72.5°	17.8
75°	15.7
77.5°	10.4
80°	7.3
82.5°	5.2
85°	3.1
87.5°	2.1
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)