

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P754168

Luminaire Tested: LD4D80BD010-EU4DR5570959027-4LBCSSQMB

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P754168
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-52)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D80BD010-EU4DR5570959027-4LBCSSQMB
Description: 4 INCH SQAURE SHALLOW CAST MATTE BLACK TRIM, WITH 55° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7424.4 lumens
Efficiency: N/A
Efficacy: 94.1 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.87
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 78.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P754168

CATALOG NUMBER: LD4D80BD010-EU4DR5570959027-4LBCSSQMB

Luminous Intensity Polar Plot





TEST NUMBER: P754168

CATALOG NUMBER: LD4D80BD010-EU4DR5570959027-4LBCSSQMB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	100	100													
	1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94	94	94	94	94	94													
	2	108	103	99	96	106	101	98	95	98	95	92	95	93	90	92	90	89	87	87	87	87	87	87													
	3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81	81	81	81	81	81													
	4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77	75	75	75	75	75	75													
	5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70	70	70	70	70	70													
	6	88	79	73	68	86	78	72	68	76	71	68	75	70	67	74	70	67	65	65	65	65	65	65													
	7	83	74	68	64	82	73	67	63	72	67	63	71	66	63	70	65	62	61	61	61	61	61	61													
	8	79	69	63	59	78	69	63	59	68	63	59	67	62	59	66	62	58	57	57	57	57	57	57													
	9	75	66	60	56	74	65	59	55	64	59	55	63	58	55	62	58	55	54	54	54	54	54	54													
	10	72	62	56	52	71	61	56	52	61	56	52	60	55	52	59	55	52	50	50	50	50	50	50													

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	909629
5°	873498
10°	870207
15°	845218
20°	757855
25°	626324
30°	473113
35°	343047
40°	219536
45°	100267
50°	32789
55°	14153
60°	6097
65°	801
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 100267 cd/sqm



TEST NUMBER: P754168

CATALOG NUMBER: LD4D80BD010-EU4DR5570959027-4LBCSSQMB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	757.8	10.2
10°-20°	2068.3	27.9
20°-30°	2357.0	31.7
30°-40°	1604.6	21.6
40°-50°	552.9	7.4
50°-60°	76.4	1.0
60°-70°	7.4	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5183.1	69.8
0°-40°	6787.7	91.4
0°-60°	7417.0	99.9
0°-90°	7424.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7424.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8325	
5°	7964	758
15°	7472	2068
25°	5195	2357
35°	2572	1605
45°	649	553
55°	74	76
65°	3	7
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P754168

CATALOG NUMBER: LD4D80BD010-EU4DR5570959027-4LBCSSQMB

CANDELA DISTRIBUTION (FULL):

	0°
0°	8325.3
2.5°	8134.5
5°	7964.2
7.5°	7880.7
10°	7843.5
12.5°	7719.8
15°	7472.2
17.5°	7079.1
20°	6517.9
22.5°	5870.0
25°	5195.3
27.5°	4492.8
30°	3750.0
32.5°	3120.7
35°	2571.9
37.5°	2049.9
40°	1539.2
42.5°	1066.7
45°	648.9
47.5°	349.7
50°	192.9
52.5°	114.5
55°	74.3
57.5°	47.5
60°	27.9
62.5°	12.4
65°	3.1
67.5°	1.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)