

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P756701

Luminaire Tested: LD4D95BD010-EU4DR6570959035-4LBSQW1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P756701
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D95BD010-EU4DR6570959035-4LBSQW1B
Description: 4 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5965.3 lumens
Efficiency: N/A
Efficacy: 60.1 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P756701
CATALOG NUMBER: LD4D95BD010-EU4DR6570959035-4LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P756701

CATALOG NUMBER: LD4D95BD010-EU4DR6570959035-4LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93																			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87																			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80																			
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69																			
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65																			
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60																			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57																			
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53																			
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	641710
5°	642242
10°	664857
15°	665954
20°	613118
25°	522405
30°	399926
35°	282545
40°	166777
45°	67710
50°	24545
55°	13677
60°	7845
65°	4318
70°	4536
75°	3504
80°	3649
85°	3134

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 67710 cd/sqm



TEST NUMBER: P756701

CATALOG NUMBER: LD4D95BD010-EU4DR6570959035-4LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	565.5	9.5
10°-20°	1631.3	27.3
20°-30°	1957.3	32.8
30°-40°	1315.4	22.1
40°-50°	393.8	6.6
50°-60°	69.5	1.2
60°-70°	19.8	0.3
70°-80°	9.7	0.2
80°-90°	3.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4154.2	69.6
0°-40°	5469.5	91.7
0°-60°	5932.8	99.5
0°-90°	5965.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5965.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5873	
5°	5856	566
15°	5887	1631
25°	4333	1957
35°	2118	1315
45°	438	394
55°	72	69
65°	17	20
75°	8	10
85°	2	3
90°	0	



TEST NUMBER: P756701

CATALOG NUMBER: LD4D95BD010-EU4DR6570959035-4LBSQW1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	5873.2
2.5°	5898.3
5°	5855.7
7.5°	5944.2
10°	5992.6
12.5°	5980.9
15°	5887.4
17.5°	5658.7
20°	5273.1
22.5°	4819.1
25°	4333.3
27.5°	3785.0
30°	3169.9
32.5°	2612.4
35°	2118.3
37.5°	1630.0
40°	1169.3
42.5°	763.7
45°	438.2
47.5°	232.0
50°	144.4
52.5°	100.2
55°	71.8
57.5°	51.7
60°	35.9
62.5°	23.4
65°	16.7
67.5°	15.0
70°	14.2
72.5°	10.9
75°	8.3
77.5°	7.5
80°	5.8
82.5°	4.2
85°	2.5
87.5°	1.7
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)