

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P756705

Luminaire Tested: LD4D95BD010-EU4DR6570959040-4LBCSSQMW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P756705
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D95BD010-EU4DR6570959040-4LBCSSQMW
Description: 4 INCH SQAURE SHALLOW CAST MATTE WHITE TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8347.3 lumens
Efficiency: N/A
Efficacy: 84.1 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P756705
CATALOG NUMBER: LD4D95BD010-EU4DR6570959040-4LBCSSQMW

Luminous Intensity Polar Plot





TEST NUMBER: P756705

CATALOG NUMBER: LD4D95BD010-EU4DR6570959040-4LBCSSQMW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93																			
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85																			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78																			
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72																			
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66																			
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61																			
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56																			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52																			
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49																			
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	442649
5°	441531
10°	441157
15°	427560
20°	389240
25°	339194
30°	282117
35°	223533
40°	161333
45°	101923
50°	53126
55°	28236
60°	14835
65°	8154
70°	3415
75°	3768
80°	2623
85°	2211

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 101923 cd/sqm



TEST NUMBER: P756705

CATALOG NUMBER: LD4D95BD010-EU4DR6570959040-4LBCSSQMW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	716.7	8.6
10°-20°	1962.7	23.5
20°-30°	2399.1	28.7
30°-40°	1946.6	23.3
40°-50°	970.0	11.6
50°-60°	270.6	3.2
60°-70°	61.5	0.7
70°-80°	16.0	0.2
80°-90°	4.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5078.6	60.8
0°-40°	7025.2	84.2
0°-60°	8265.7	99.0
0°-90°	8347.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8347.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7579	
5°	7531	717
15°	7071	1963
25°	5264	2399
35°	3135	1947
45°	1234	970
55°	277	271
65°	59	61
75°	17	16
85°	3	4
90°	0	



TEST NUMBER: P756705

CATALOG NUMBER: LD4D95BD010-EU4DR6570959040-4LBCSSQMW

CANDELA DISTRIBUTION (FULL):

	0°
0°	7579.1
2.5°	7573.6
5°	7531.2
7.5°	7506.7
10°	7438.8
12.5°	7300.7
15°	7071.3
17.5°	6712.6
20°	6262.7
22.5°	5777.1
25°	5263.6
27.5°	4714.5
30°	4183.3
32.5°	3658.7
35°	3135.2
37.5°	2612.9
40°	2116.1
42.5°	1650.6
45°	1234.0
47.5°	859.8
50°	584.7
52.5°	403.2
55°	277.3
57.5°	187.1
60°	127.0
62.5°	88.0
65°	59.0
67.5°	30.1
70°	20.0
72.5°	18.9
75°	16.7
77.5°	11.1
80°	7.8
82.5°	5.6
85°	3.3
87.5°	2.2
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)