

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P756493

Luminaire Tested: LD4D95BD010-EU4DR5070959050-4LBSQW1B

Issue Date: 1/30/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P756493  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-44)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 1/30/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D95BD010-EU4DR5070959050-4LBSQW1B  
Description: 4 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 50° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8488.6 lumens  
Efficiency: N/A  
Efficacy: 85.6 lumens/watt  
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.73  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 99.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P756493  
CATALOG NUMBER: LD4D95BD010-EU4DR5070959050-4LBSQW1B

### Luminous Intensity Polar Plot





TEST NUMBER: P756493  
 CATALOG NUMBER: LD4D95BD010-EU4DR5070959050-4LBSQW1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	114	112	109	107	112	110	108	106	106	104	102	102	101	99	98	97	97	95				
2	109	105	101	98	107	103	100	97	100	98	95	97	95	93	95	93	91	90				
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	85				
4	100	94	89	85	99	93	88	85	90	87	84	89	85	83	87	84	82	80				
5	96	89	84	80	95	88	83	79	86	82	79	85	81	78	83	80	77	76				
6	92	84	79	75	91	83	79	75	82	78	74	81	77	74	79	76	74	72				
7	88	80	75	71	87	79	74	71	78	74	71	77	73	70	76	73	70	69				
8	85	76	71	67	84	76	71	67	75	70	67	74	70	67	73	69	66	65				
9	81	73	68	64	80	72	67	64	71	67	64	71	67	64	70	66	63	62				
10	78	70	64	61	77	69	64	61	68	64	61	68	64	61	67	63	60	59				

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1494381
5°	1478713
10°	1454361
15°	1324317
20°	1101976
25°	782239
30°	414043
35°	168729
40°	62657
45°	28694
50°	11763
55°	6153
60°	3016
65°	905
70°	0
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 28694 cd/sqm



TEST NUMBER: P756493

CATALOG NUMBER: LD4D95BD010-EU4DR5070959050-4LBSQW1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1274.3	15.0
10°-20°	3220.6	37.9
20°-30°	2892.9	34.1
30°-40°	905.8	10.7
40°-50°	158.6	1.9
50°-60°	31.6	0.4
60°-70°	4.8	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	7387.8	87.0
0°-40°	8293.6	97.7
0°-60°	8483.8	99.9
0°-90°	8488.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8488.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	13677	
5°	13482	###
15°	11708	3221
25°	6489	2893
35°	1265	906
45°	186	159
55°	32	32
65°	4	5
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P756493

CATALOG NUMBER: LD4D95BD010-EU4DR5070959050-4LBSQW1B

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	13677.2
2.5°	13609.2
5°	13482.3
7.5°	13288.6
10°	13108.7
12.5°	12532.2
15°	11707.7
17.5°	10660.6
20°	9477.5
22.5°	8108.8
25°	6488.6
27.5°	4770.5
30°	3281.8
32.5°	2136.7
35°	1265.0
37.5°	726.5
40°	439.3
42.5°	286.0
45°	185.7
47.5°	113.0
50°	69.2
52.5°	47.3
55°	32.3
57.5°	21.9
60°	13.8
62.5°	8.1
65°	3.5
67.5°	1.2
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)