

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P754128

Luminaire Tested: LD4D80BD010-EU4DR5070959035-4LBSQW1MW

Issue Date: 1/30/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P754128  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-44)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 1/30/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D80BD010-EU4DR5070959035-4LBSQW1MW  
Description: 4 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 50° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7381.8 lumens  
Efficiency: N/A  
Efficacy: 93.6 lumens/watt  
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.73  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct


Input Watts (W): 78.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P754128

CATALOG NUMBER: LD4D80BD010-EU4DR5070959035-4LBSQW1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P754128

CATALOG NUMBER: LD4D80BD010-EU4DR5070959035-4LBSQW1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	114	112	109	107	112	110	108	106	106	104	102	102	101	99	98	97	97	95			95
2	109	105	101	98	107	103	100	97	100	98	95	97	95	93	95	93	91	90			90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	85			85
4	100	94	89	85	99	93	88	85	90	87	84	89	85	83	87	84	82	80			80
5	96	89	84	80	95	88	83	79	86	82	79	85	81	78	83	80	77	76			76
6	92	84	79	75	91	83	79	75	82	78	74	81	77	74	79	76	74	72			72
7	88	80	75	71	87	79	74	71	78	74	71	77	73	70	76	73	70	69			69
8	85	76	71	67	84	76	71	67	75	70	67	74	70	67	73	69	66	65			65
9	81	73	68	64	80	72	67	64	71	67	64	71	67	64	70	66	63	62			62
10	78	70	64	61	77	69	64	61	68	64	61	68	64	61	67	63	60	59			59

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1299536
5°	1285910
10°	1264732
15°	1151636
20°	958298
25°	680249
30°	360058
35°	146721
40°	54499
45°	24939
50°	10233
55°	5353
60°	2622
65°	776
70°	0
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 24939 cd/sqm



TEST NUMBER: P754128

CATALOG NUMBER: LD4D80BD010-EU4DR5070959035-4LBSQW1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1108.2	15.0
10°-20°	2800.6	37.9
20°-30°	2515.7	34.1
30°-40°	787.6	10.7
40°-50°	137.9	1.9
50°-60°	27.5	0.4
60°-70°	4.1	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6424.5	87.0
0°-40°	7212.2	97.7
0°-60°	7377.6	99.9
0°-90°	7381.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7381.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	11894	
5°	11724	###
15°	10181	2801
25°	5643	2516
35°	1100	788
45°	161	138
55°	28	28
65°	3	4
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P754128

CATALOG NUMBER: LD4D80BD010-EU4DR5070959035-4LBSQW1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	11893.9
2.5°	11834.7
5°	11724.4
7.5°	11555.9
10°	11399.5
12.5°	10898.1
15°	10181.1
17.5°	9270.6
20°	8241.8
22.5°	7051.5
25°	5642.6
27.5°	4148.5
30°	2853.9
32.5°	1858.1
35°	1100.0
37.5°	631.7
40°	382.1
42.5°	248.7
45°	161.4
47.5°	98.3
50°	60.2
52.5°	41.1
55°	28.1
57.5°	19.1
60°	12.0
62.5°	7.0
65°	3.0
67.5°	1.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)