

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206822

Luminaire Tested: **LD4B10D010 EU4B10209024 4LBWGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P206822
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B10D010 EU4B10209024 4LBWGPH1
Description: PORTFOLIO 4 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 507.5 lumens
Efficiency: N/A
Efficacy: 51.3 lumens/watt
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P206822

CATALOG NUMBER: LD4B10D010 EU4B10209024 4LBWGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P206822

CATALOG NUMBER: LD4B10D010 EU4B10209024 4LBWGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100											100																	
1	113	110	107	104	110	107	105	103	103	101	99	100	98	96	96	95	94	92											92																	
2	106	100	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83											83																	
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	77	76											76																	
4	94	85	78	74	92	84	78	73	81	76	72	79	75	71	77	74	71	69											69																	
5	88	78	72	67	86	77	71	66	75	70	66	74	69	65	72	68	64	63											63																	
6	83	72	65	61	81	71	65	60	70	64	60	68	63	59	67	63	59	57											57																	
7	78	67	60	55	76	66	60	55	65	59	55	64	58	55	63	58	54	53											53																	
8	73	62	56	51	72	62	55	51	61	55	51	59	54	50	58	54	50	48											48																	
9	69	58	51	47	68	58	51	47	57	51	47	56	50	46	55	50	46	45											45																	
10	65	54	48	43	64	54	48	43	53	47	43	52	47	43	51	46	43	42											42																	

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P206822

CATALOG NUMBER: LD4B10D010 EU4B10209024 4LBWGP1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	34.5	6.8
10°-20°	97.7	19.2
20°-30°	140.0	27.6
30°-40°	131.9	26.0
40°-50°	72.8	14.3
50°-60°	23.4	4.6
60°-70°	5.8	1.1
70°-80°	1.4	0.3
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	272.2	53.6
0°-40°	404.0	79.6
0°-60°	500.2	98.6
0°-90°	507.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	507.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	365	
5°	364	34
15°	346	98
25°	307	140
35°	214	132
45°	92	73
55°	24	23
65°	5	6
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P206822

CATALOG NUMBER: LD4B10D010 EU4B10209024 4LBWGPH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	365.3
2.5°	362.7
5°	363.6
7.5°	360.9
10°	356.5
12.5°	352.1
15°	346.0
17.5°	340.7
20°	331.9
22.5°	319.5
25°	307.2
27.5°	290.5
30°	268.5
32.5°	243.8
35°	213.9
37.5°	182.2
40°	149.6
42.5°	119.7
45°	92.4
47.5°	69.5
50°	50.2
52.5°	35.2
55°	23.8
57.5°	15.8
60°	11.4
62.5°	7.9
65°	5.3
67.5°	3.5
70°	2.6
72.5°	1.8
75°	0.9
77.5°	0.9
80°	0.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)