

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206093

Luminaire Tested: **LD4B10D010 EU4B10208027 4LBSMW1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P206093  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD4B10D010 EU4B10208027 4LBSMW1  
Description: PORTFOLIO 4 INCH SHALLOW RECESSED DOWNLIGHT  
SHALLOW DISTRIBUTION WITH MATTE WHITE TRIM  
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W  
DL3-11.1W DLE-11.39W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1052.0 lumens  
Efficiency: N/A  
Efficacy: 106.3 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 9.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P206093

CATALOG NUMBER: LD4B10D010 EU4B10208027 4LBSMW1

### Luminous Intensity Polar Plot






TEST NUMBER: P206093

CATALOG NUMBER: LD4B10D010 EU4B10208027 4LBSMW1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86				86
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74				74
3	93	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63				63
4	85	74	65	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54				54
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	49	47				47
6	73	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42				42
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	43	39	37				37
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	33				33
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30				30
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27				27

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P206093

CATALOG NUMBER: LD4B10D010 EU4B10208027 4LBSMW1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	40.2	3.8
10°-20°	114.5	10.9
20°-30°	172.4	16.4
30°-40°	205.1	19.5
40°-50°	204.8	19.5
50°-60°	166.6	15.8
60°-70°	102.4	9.7
70°-80°	39.7	3.8
80°-90°	6.4	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	327.0	31.1
0°-40°	532.2	50.6
0°-60°	903.5	85.9
0°-90°	1052.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1052.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	424	
5°	423	40
15°	406	114
25°	375	172
35°	328	205
45°	266	205
55°	186	167
65°	103	102
75°	36	40
85°	5	6
90°	0	



TEST NUMBER: P206093

CATALOG NUMBER: LD4B10D010 EU4B10208027 4LBSMW1

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	423.9
2.5°	424.5
5°	422.6
7.5°	420.1
10°	417.0
12.5°	411.4
15°	406.4
17.5°	398.9
20°	390.8
22.5°	383.3
25°	375.2
27.5°	364.0
30°	352.8
32.5°	342.2
35°	328.5
37.5°	313.5
40°	299.8
42.5°	283.0
45°	266.2
47.5°	248.1
50°	228.8
52.5°	208.8
55°	186.4
57.5°	164.6
60°	143.4
62.5°	122.8
65°	102.8
67.5°	84.1
70°	66.7
72.5°	50.5
75°	36.2
77.5°	23.7
80°	14.3
82.5°	8.7
85°	5.0
87.5°	2.5
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)