

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P35173

Luminaire Tested: **LD4B10D010 EU4B10209027 4LBMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P35173
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B10D010 EU4B10209027 4LBMH1
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 662.6 lumens
Efficiency: N/A
Efficacy: 68.0 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 9.74
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P35173

CATALOG NUMBER: LD4B10D010 EU4B10209027 4LBMH1

Luminous Intensity Polar Plot





TEST NUMBER: P35173

CATALOG NUMBER: LD4B10D010 EU4B10209027 4LBMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93	93	93	93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85	85	85	85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	82	86	83	80	79	79	79	79
4	96	88	82	77	94	86	81	77	84	80	76	82	78	75	80	77	74	73	73	73	73
5	90	82	75	71	89	81	75	70	79	74	70	77	73	69	75	72	69	67	67	67	67
6	86	76	70	65	84	75	69	65	74	68	64	72	68	64	71	67	64	62	62	62	62
7	81	71	65	60	80	70	64	60	69	64	60	68	63	59	67	62	59	58	58	58	58
8	77	67	60	56	75	66	60	56	65	59	56	64	59	55	63	58	55	54	54	54	54
9	73	63	56	52	72	62	56	52	61	56	52	60	55	52	59	55	52	50	50	50	50
10	69	59	53	49	68	59	53	49	58	52	49	57	52	48	56	52	48	47	47	47	47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	71784
5°	70742
10°	67788
15°	64023
20°	59764
25°	54250
30°	45293
35°	32812
40°	20539
45°	11743
50°	6119
55°	3429
60°	2185
65°	1293
70°	958
75°	422
80°	629
85°	0



TEST NUMBER: P35173

CATALOG NUMBER: LD4B10D010 EU4B10209027 4LBMH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	60.5	9.1
10°-20°	158.6	23.9
20°-30°	203.8	30.8
30°-40°	153.4	23.1
40°-50°	61.6	9.3
50°-60°	17.5	2.6
60°-70°	5.5	0.8
70°-80°	1.6	0.2
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	422.9	63.8
0°-40°	576.2	87.0
0°-60°	655.3	98.9
0°-90°	662.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	662.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	657	
5°	645	60
15°	566	159
25°	450	204
35°	246	153
45°	76	62
55°	18	18
65°	5	6
75°	1	2
85°	0	0
90°	0	



TEST NUMBER: P35173

CATALOG NUMBER: LD4B10D010 EU4B10209027 4LBMH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	657
2.5°	653
5°	645
7.5°	630
10°	611
12.5°	588
15°	566
17.5°	541
20°	514
22.5°	485
25°	450
27.5°	408
30°	359
32.5°	304
35°	246
37.5°	192
40°	144
42.5°	106
45°	76
47.5°	52
50°	36
52.5°	25
55°	18
57.5°	13
60°	10
62.5°	7
65°	5
67.5°	4
70°	3
72.5°	2
75°	1
77.5°	1
80°	1
82.5°	0
85°	0
87.5°	0
90°	0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)