

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P754377

Luminaire Tested: LD4D80BD010-EU4DR6570959050-4LBCSSQMMS

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P754377  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D80BD010-EU4DR6570959050-4LBCSSQMMMS  
Description: 4 INCH SQAURE SHALLOW CAST MATTE METALLIC SILVER TRIM, WITH 65° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7134.5 lumens  
Efficiency: N/A  
Efficacy: 90.4 lumens/watt  
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96  
Luminous Opening: Circular (Dia: 0.48' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 78.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P754377

CATALOG NUMBER: LD4D80BD010-EU4DR6570959050-4LBCSSQMMS

### Luminous Intensity Polar Plot





TEST NUMBER: P754377

CATALOG NUMBER: LD4D80BD010-EU4DR6570959050-4LBCSSQMMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10		0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93			
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78			
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72			
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66			
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61			
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52			
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49			
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	378334
5°	377382
10°	377060
15°	365433
20°	332682
25°	289916
30°	241128
35°	191057
40°	137897
45°	87114
50°	45412
55°	24132
60°	12674
65°	6979
70°	2920
75°	3227
80°	2253
85°	1943

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 87114 cd/sqm



TEST NUMBER: P754377

CATALOG NUMBER: LD4D80BD010-EU4DR6570959050-4LBCSSQMMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	612.6	8.6
10°-20°	1677.5	23.5
20°-30°	2050.5	28.7
30°-40°	1663.7	23.3
40°-50°	829.1	11.6
50°-60°	231.2	3.2
60°-70°	52.6	0.7
70°-80°	13.7	0.2
80°-90°	3.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4340.7	60.8
0°-40°	6004.4	84.2
0°-60°	7064.7	99.0
0°-90°	7134.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7134.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	6478	
5°	6437	613
15°	6044	1678
25°	4499	2051
35°	2680	1664
45°	1055	829
55°	237	231
65°	50	53
75°	14	14
85°	3	4
90°	0	



TEST NUMBER: P754377

CATALOG NUMBER: LD4D80BD010-EU4DR6570959050-4LBCSSQMMS

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	6477.9
2.5°	6473.2
5°	6437.0
7.5°	6416.1
10°	6358.0
12.5°	6239.9
15°	6043.8
17.5°	5737.3
20°	5352.7
22.5°	4937.7
25°	4498.9
27.5°	4029.5
30°	3575.5
32.5°	3127.1
35°	2679.7
37.5°	2233.2
40°	1808.7
42.5°	1410.8
45°	1054.7
47.5°	734.9
50°	499.8
52.5°	344.6
55°	237.0
57.5°	159.9
60°	108.5
62.5°	75.2
65°	50.5
67.5°	25.7
70°	17.1
72.5°	16.2
75°	14.3
77.5°	9.5
80°	6.7
82.5°	4.8
85°	2.9
87.5°	1.9
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)