

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P35208

Luminaire Tested: **LD4B10D010 EU4B10209027 4LBNB1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P35208  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD4B10D010 EU4B10209027 4LBNB1  
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT  
NARROW DISTRIBUTION WITH SPECULAR BLACK TRIM  
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W  
DL3-11.1W DLE-11.39W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 341.9 lumens  
Efficiency: N/A  
Efficacy: 35.1 lumens/watt  
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.79  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct


Input Watts (W): 9.73  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P35208

CATALOG NUMBER: LD4B10D010 EU4B10209027 4LBNB1

### Luminous Intensity Polar Plot





TEST NUMBER: P35208

CATALOG NUMBER: LD4B10D010 EU4B10209027 4LBNB1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94			
2	109	104	100	97	106	102	99	96	99	96	94	96	94	92	93	92	90	88			
3	104	98	93	89	102	96	92	88	94	90	87	91	88	86	89	86	84	83			
4	99	92	86	82	97	90	86	82	88	84	81	86	83	80	85	82	79	78			
5	94	86	81	77	92	85	80	76	84	79	76	82	78	75	80	77	74	73			
6	90	81	76	72	88	81	75	71	79	74	71	78	74	70	76	73	70	69			
7	86	77	71	67	84	76	71	67	75	70	67	74	69	66	73	69	66	65			
8	82	73	67	63	80	72	67	63	71	66	63	70	66	62	69	65	62	61			
9	78	69	63	60	77	68	63	59	67	63	59	67	62	59	66	62	59	58			
10	75	65	60	56	74	65	60	56	64	59	56	63	59	56	63	59	56	54			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	61077
5°	56813
10°	47818
15°	39703
20°	34300
25°	30501
30°	24980
35°	15339
40°	6133
45°	1391
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P35208

CATALOG NUMBER: LD4B10D010 EU4B10209027 4LBNB1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	46.6	13.6
10°-20°	98.8	28.9
20°-30°	114.6	33.5
30°-40°	71.8	21.0
40°-50°	10.1	3.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	260.0	76.0
0°-40°	331.8	97.0
0°-60°	341.9	100.0
0°-90°	341.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	341.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	559	
5°	518	47
15°	351	99
25°	253	115
35°	115	72
45°	9	10
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P35208

CATALOG NUMBER: LD4B10D010 EU4B10209027 4LBNB1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	559
2.5°	548
5°	518
7.5°	475
10°	431
12.5°	389
15°	351
17.5°	319
20°	295
22.5°	273
25°	253
27.5°	229
30°	198
32.5°	159
35°	115
37.5°	75
40°	43
42.5°	22
45°	9
47.5°	2
50°	0
52.5°	0
55°	0
57.5°	0
60°	0
62.5°	0
65°	0
67.5°	0
70°	0
72.5°	0
75°	0
77.5°	0
80°	0
82.5°	0
85°	0
87.5°	0
90°	0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)