

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P754791

Luminaire Tested: LD4D85BD010-EU4DR4570959024-4LBSQW1MW

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P754791
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D85BD010-EU4DR4570959024-4LBSQW1MW
Description: 4 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 45° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6537.9 lumens
Efficiency: N/A
Efficacy: 74.5 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.69
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 87.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P754791

CATALOG NUMBER: LD4D85BD010-EU4DR4570959024-4LBSQW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P754791

CATALOG NUMBER: LD4D85BD010-EU4DR4570959024-4LBSQW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100														
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	98	98	97	95					95														
2	109	105	102	99	107	103	100	98	100	98	95	97	95	93	95	93	91	90					90														
3	105	99	95	91	103	98	94	91	95	92	89	93	90	88	91	89	87	85					85														
4	100	94	89	85	99	93	88	85	91	87	84	89	86	83	87	84	82	81					81														
5	96	89	84	80	95	88	83	80	86	82	79	85	81	79	83	80	78	77					77														
6	92	85	80	76	91	84	79	76	83	78	75	81	77	75	80	77	74	73					73														
7	89	81	75	72	87	80	75	72	79	74	71	78	74	71	77	73	71	69					69														
8	85	77	72	68	84	76	71	68	75	71	68	74	70	67	73	70	67	66					66														
9	82	73	68	65	81	73	68	65	72	68	65	71	67	64	71	67	64	63					63														
10	79	70	65	62	78	70	65	62	69	65	62	68	64	61	68	64	61	60					60														

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1262606
5°	1226651
10°	1173579
15°	1074073
20°	852106
25°	531977
30°	293216
35°	131662
40°	51860
45°	24429
50°	11593
55°	6058
60°	2972
65°	698
70°	288
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 24429 cd/sqm



TEST NUMBER: P754791

CATALOG NUMBER: LD4D85BD010-EU4DR4570959024-4LBSQW1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1050.9	16.1
10°-20°	2586.3	39.6
20°-30°	2048.1	31.3
30°-40°	682.0	10.4
40°-50°	135.4	2.1
50°-60°	30.7	0.5
60°-70°	4.4	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5685.2	87.0
0°-40°	6367.2	97.4
0°-60°	6533.3	99.9
0°-90°	6537.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6537.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	11556	
5°	11184	###
15°	9495	2586
25°	4413	2048
35°	987	682
45°	158	135
55°	32	31
65°	3	4
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P754791

CATALOG NUMBER: LD4D85BD010-EU4DR4570959024-4LBSQW1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	11555.9
2.5°	11480.4
5°	11184.1
7.5°	10939.6
10°	10577.9
12.5°	10096.1
15°	9495.4
17.5°	8591.9
20°	7328.5
22.5°	5823.4
25°	4412.7
27.5°	3231.2
30°	2324.1
32.5°	1580.6
35°	987.1
37.5°	585.3
40°	363.6
42.5°	239.0
45°	158.1
47.5°	101.8
50°	68.2
52.5°	45.4
55°	31.8
57.5°	20.9
60°	13.6
62.5°	7.3
65°	2.7
67.5°	0.9
70°	0.9
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)