

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205995

Luminaire Tested: **LD4B10D010 EU4B10209027 4LBSB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205995
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B10D010 EU4B10209027 4LBSB1
Description: PORTFOLIO 4 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH SPECULAR BLACK TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 761.1 lumens
Efficiency: N/A
Efficacy: 76.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.3
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205995

CATALOG NUMBER: LD4B10D010 EU4B10209027 4LBSB1

Luminous Intensity Polar Plot





TEST NUMBER: P205995

CATALOG NUMBER: LD4B10D010 EU4B10209027 4LBSB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	103	100	108	105	101	98	100	98	95	97	94	93	93	91	90	88			88
2	102	95	89	84	100	93	88	83	90	85	81	86	83	79	84	80	78	76			76
3	94	84	77	72	91	83	76	71	80	74	70	77	73	68	75	71	67	65			65
4	86	76	68	62	84	74	67	61	72	65	60	70	64	60	68	63	59	57			57
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50			50
6	74	62	53	47	72	61	53	47	59	52	47	57	51	46	56	50	46	44			44
7	69	56	48	42	67	55	48	42	54	47	42	52	46	41	51	45	41	39			39
8	64	51	43	38	63	51	43	38	49	42	37	48	42	37	47	41	37	35			35
9	60	47	39	34	59	47	39	34	46	39	34	45	38	34	44	38	34	32			32
10	56	44	36	31	55	43	36	31	42	36	31	41	35	31	40	35	31	29			29

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205995

CATALOG NUMBER: LD4B10D010 EU4B10209027 4LBSB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	31.7	4.2
10°-20°	89.9	11.8
20°-30°	133.8	17.6
30°-40°	155.6	20.4
40°-50°	151.7	19.9
50°-60°	116.7	15.3
60°-70°	64.5	8.5
70°-80°	17.1	2.2
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	255.4	33.5
0°-40°	411.0	54.0
0°-60°	679.4	89.3
0°-90°	761.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	761.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	336	
5°	334	32
15°	318	90
25°	290	134
35°	250	156
45°	197	152
55°	130	117
65°	65	65
75°	14	17
85°	0	0
90°	0	



TEST NUMBER: P205995

CATALOG NUMBER: LD4B10D010 EU4B10209027 4LBSB1

CANDELA DISTRIBUTION (FULL):

	0°
0°	335.7
2.5°	335.7
5°	333.8
7.5°	330.9
10°	329.0
12.5°	323.2
15°	318.4
17.5°	313.6
20°	306.8
22.5°	300.0
25°	290.4
27.5°	280.8
30°	271.1
32.5°	260.5
35°	249.9
37.5°	236.4
40°	224.8
42.5°	212.3
45°	196.8
47.5°	182.3
50°	165.9
52.5°	148.6
55°	130.2
57.5°	112.9
60°	96.5
62.5°	80.1
65°	64.6
67.5°	50.2
70°	36.7
72.5°	25.1
75°	14.5
77.5°	6.8
80°	1.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)