

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205580

Luminaire Tested: **LD4B10D010 EU4B10209027 4LBSWMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205580
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B10D010 EU4B10209027 4LBSWMH1
Description: PORTFOLIO 4 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH WARM HAZE TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 877.9 lumens
Efficiency: N/A
Efficacy: 88.7 lumens/watt
Spacing Criteria (0/90/45): 0.99 / 0.99 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205580

CATALOG NUMBER: LD4B10D010 EU4B10209027 4LBSWMH1

Luminous Intensity Polar Plot





TEST NUMBER: P205580

CATALOG NUMBER: LD4B10D010 EU4B10209027 4LBSWMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	108	105	102	109	106	103	101	102	100	97	98	96	94	95	93	92	90																			
2	104	98	92	88	102	96	91	87	92	88	85	89	86	83	86	84	81	79																			
3	96	88	82	76	94	87	81	76	84	79	74	81	77	73	79	75	72	70																			
4	90	80	73	67	88	79	72	67	76	70	66	74	69	65	72	68	64	62																			
5	83	73	65	59	82	72	64	59	70	63	59	68	62	58	66	61	57	56																			
6	78	66	59	53	76	65	58	53	64	57	53	62	57	52	61	56	52	50																			
7	73	61	53	48	71	60	53	48	59	52	48	57	52	47	56	51	47	45																			
8	68	56	49	44	67	56	48	43	54	48	43	53	47	43	52	47	43	41																			
9	64	52	45	40	63	52	45	40	50	44	40	49	44	39	49	43	39	38																			
10	60	48	41	37	59	48	41	37	47	41	36	46	40	36	45	40	36	35																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205580

CATALOG NUMBER: LD4B10D010 EU4B10209027 4LBSWMH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.4	5.9
10°-20°	136.3	15.5
20°-30°	183.0	20.8
30°-40°	187.4	21.3
40°-50°	162.2	18.5
50°-60°	107.8	12.3
60°-70°	44.3	5.0
70°-80°	5.3	0.6
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	370.7	42.2
0°-40°	558.1	63.6
0°-60°	828.1	94.3
0°-90°	877.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	877.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	556	
5°	548	51
15°	487	136
25°	399	183
35°	299	187
45°	211	162
55°	120	108
65°	44	44
75°	2	5
85°	0	0
90°	0	



TEST NUMBER: P205580

CATALOG NUMBER: LD4B10D010 EU4B10209027 4LBSWMH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	556.4
2.5°	555.2
5°	547.8
7.5°	536.3
10°	520.7
12.5°	503.5
15°	486.8
17.5°	465.5
20°	444.8
22.5°	422.9
25°	399.3
27.5°	374.0
30°	348.7
32.5°	323.4
35°	299.2
37.5°	276.2
40°	254.3
42.5°	232.5
45°	211.2
47.5°	188.7
50°	165.7
52.5°	142.7
55°	119.7
57.5°	99.5
60°	78.8
62.5°	59.8
65°	43.7
67.5°	28.8
70°	16.7
72.5°	8.1
75°	2.3
77.5°	1.2
80°	0.6
82.5°	0.6
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)