

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P754637

Luminaire Tested: LD4D85BD010-EU4DR3570959027-4LBCSSQMMS

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P754637
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D85BD010-EU4DR3570959027-4LBCSSQMMMS
Description: 4 INCH SQAURE SHALLOW CAST MATTE METALLIC SILVER TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7228.3 lumens
Efficiency: N/A
Efficacy: 82.4 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 87.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P754637
CATALOG NUMBER: LD4D85BD010-EU4DR3570959027-4LBCSSQMMS

Luminous Intensity Polar Plot





TEST NUMBER: P754637

CATALOG NUMBER: LD4D85BD010-EU4DR3570959027-4LBCSSQMMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20								
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	98	96																											
2	110	106	103	101	108	105	102	99	102	99	97	99	97	95	96	95	93	92																											
3	106	101	97	94	105	100	96	93	97	95	92	95	93	91	93	91	89	88																											
4	103	97	92	89	101	96	92	89	94	90	88	92	89	87	90	88	86	84																											
5	99	93	88	85	98	92	87	84	90	86	84	89	85	83	87	84	82	81																											
6	96	89	84	81	94	88	84	81	87	83	80	85	82	80	84	81	79	78																											
7	93	85	81	78	91	85	80	77	84	80	77	83	79	77	82	79	76	75																											
8	90	82	78	74	88	82	77	74	81	77	74	80	76	74	79	76	73	72																											
9	87	79	75	72	86	79	75	72	78	74	71	77	74	71	77	73	71	70																											
10	84	77	72	69	83	76	72	69	76	72	69	75	71	69	74	71	69	68																											

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2173033
5°	2121975
10°	1912459
15°	1484375
20°	841909
25°	327538
30°	122202
35°	66985
40°	43773
45°	26654
50°	16964
55°	11982
60°	8763
65°	4757
70°	351
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 26654 cd/sqm



TEST NUMBER: P754637

CATALOG NUMBER: LD4D85BD010-EU4DR3570959027-4LBCSSQMMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1779.4	24.6
10°-20°	3474.1	48.1
20°-30°	1416.9	19.6
30°-40°	339.1	4.7
40°-50°	141.3	2.0
50°-60°	58.5	0.8
60°-70°	18.3	0.3
70°-80°	0.4	0.0
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6670.4	92.3
0°-40°	7009.4	97.0
0°-60°	7209.2	99.7
0°-90°	7228.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7228.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	19888	
5°	19347	###
15°	13123	3474
25°	2717	1417
35°	502	339
45°	172	141
55°	63	58
65°	18	18
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P754637

CATALOG NUMBER: LD4D85BD010-EU4DR3570959027-4LBCSSQMMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	19888.5
2.5°	19769.2
5°	19347.3
7.5°	18505.6
10°	17237.7
12.5°	15452.4
15°	13122.7
17.5°	10273.4
20°	7240.8
22.5°	4617.2
25°	2716.9
27.5°	1535.8
30°	968.6
32.5°	680.0
35°	502.2
37.5°	388.3
40°	306.9
42.5°	236.4
45°	172.5
47.5°	129.1
50°	99.8
52.5°	79.2
55°	62.9
57.5°	51.0
60°	40.1
62.5°	29.3
65°	18.4
67.5°	6.5
70°	1.1
72.5°	1.1
75°	0.0
77.5°	0.0
80°	0.0
82.5°	1.1
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)