

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P755038

Luminaire Tested: LD4D85BD010-EU4DR6070959027-4LBSQW1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P755038
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D85BD010-EU4DR6070959027-4LBSQW1MW
Description: 4 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7089.2 lumens
Efficiency: N/A
Efficacy: 80.8 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 87.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P755038
CATALOG NUMBER: LD4D85BD010-EU4DR6070959027-4LBSQW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P755038

CATALOG NUMBER: LD4D85BD010-EU4DR6070959027-4LBSQW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66																			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62																			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	919899
5°	942519
10°	953905
15°	908721
20°	801213
25°	648048
30°	438342
35°	219655
40°	35629
45°	34875
50°	35577
55°	36117
60°	37105
65°	37953
70°	38846
75°	39302
80°	37941
85°	31591

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 39302 cd/sqm



TEST NUMBER: P755038

CATALOG NUMBER: LD4D85BD010-EU4DR6070959027-4LBSQW1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	821.3	11.6
10°-20°	2222.1	31.3
20°-30°	2390.8	33.7
30°-40°	1039.2	14.7
40°-50°	174.5	2.5
50°-60°	169.7	2.4
60°-70°	145.2	2.0
70°-80°	97.1	1.4
80°-90°	29.1	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5434.3	76.7
0°-40°	6473.5	91.3
0°-60°	6817.8	96.2
0°-90°	7089.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7089.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8419	
5°	8594	821
15°	8034	2222
25°	5376	2391
35°	1647	1039
45°	226	175
55°	190	170
65°	147	145
75°	93	97
85°	25	29
90°	0	



TEST NUMBER: P755038

CATALOG NUMBER: LD4D85BD010-EU4DR6070959027-4LBSQW1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	8419.3
2.5°	8656.0
5°	8593.5
7.5°	8613.2
10°	8597.9
12.5°	8420.4
15°	8033.6
17.5°	7514.2
20°	6890.8
22.5°	6223.5
25°	5375.5
27.5°	4299.5
30°	3474.4
32.5°	2677.9
35°	1646.8
37.5°	704.5
40°	249.8
42.5°	230.1
45°	225.7
47.5°	218.0
50°	209.3
52.5°	199.4
55°	189.6
57.5°	179.7
60°	169.8
62.5°	158.9
65°	146.8
67.5°	134.8
70°	121.6
72.5°	107.4
75°	93.1
77.5°	76.7
80°	60.3
82.5°	42.7
85°	25.2
87.5°	8.8
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)