

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P755105

Luminaire Tested: LD4D85BD010-EU4DR6570959027-4LBCSSQMMS

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P755105  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D85BD010-EU4DR6570959027-4LBCSSQMMMS  
Description: 4 INCH SQAURE SHALLOW CAST MATTE METALLIC SILVER TRIM, WITH 65° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6920.3 lumens  
Efficiency: N/A  
Efficacy: 78.9 lumens/watt  
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96  
Luminous Opening: Circular (Dia: 0.48' x H: 0')  
CIE Type: Direct

Input Watts (W): 87.7  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P755105  
CATALOG NUMBER: LD4D85BD010-EU4DR6570959027-4LBCSSQMMS

### Luminous Intensity Polar Plot





TEST NUMBER: P755105

CATALOG NUMBER: LD4D85BD010-EU4DR6570959027-4LBCSSQMMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93																			
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85																			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78																			
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72																			
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66																			
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61																			
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56																			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52																			
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49																			
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	366975
5°	366049
10°	365739
15°	354465
20°	322694
25°	281210
30°	233885
35°	185318
40°	133757
45°	84504
50°	44049
55°	23409
60°	12300
65°	6758
70°	2835
75°	3137
80°	2186
85°	1876

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 84504 cd/sqm



TEST NUMBER: P755105

CATALOG NUMBER: LD4D85BD010-EU4DR6570959027-4LBCSSQMMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	594.2	8.6
10°-20°	1627.2	23.5
20°-30°	1989.0	28.7
30°-40°	1613.8	23.3
40°-50°	804.2	11.6
50°-60°	224.3	3.2
60°-70°	50.9	0.7
70°-80°	13.3	0.2
80°-90°	3.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4210.4	60.8
0°-40°	5824.2	84.2
0°-60°	6852.7	99.0
0°-90°	6920.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6920.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	6283	
5°	6244	594
15°	5862	1627
25°	4364	1989
35°	2599	1614
45°	1023	804
55°	230	224
65°	49	51
75°	14	13
85°	3	3
90°	0	



TEST NUMBER: P755105

CATALOG NUMBER: LD4D85BD010-EU4DR6570959027-4LBCSSQMMMS

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	6283.4
2.5°	6278.8
5°	6243.7
7.5°	6223.4
10°	6167.1
12.5°	6052.6
15°	5862.4
17.5°	5565.0
20°	5192.0
22.5°	4789.4
25°	4363.8
27.5°	3908.6
30°	3468.1
32.5°	3033.2
35°	2599.2
37.5°	2166.2
40°	1754.4
42.5°	1368.4
45°	1023.1
47.5°	712.8
50°	484.8
52.5°	334.3
55°	229.9
57.5°	155.1
60°	105.3
62.5°	72.9
65°	48.9
67.5°	24.9
70°	16.6
72.5°	15.7
75°	13.9
77.5°	9.2
80°	6.5
82.5°	4.6
85°	2.8
87.5°	1.8
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)