

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P251973

Luminaire Tested: **LD4B10D010 EU4B10208030 4LBBA1MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P251973
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1712-453-3)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B10D010 EU4B10208030 4LBBA1MW
Description: PORTFOLIO 4 INCH BAFFLE RECESSED DOWNLIGHT, WITH MATTE WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1286.0 lumens
Efficiency: N/A
Efficacy: 128.0 lumens/watt
Spacing Criteria (0/90/45): 1.01 / 1.01 / 0.99
Luminous Opening: Circular (Dia: 0.38' x H: 0')
CIE Type: Direct


Input Watts (W): 10.05
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P251973

CATALOG NUMBER: LD4B10D010 EU4B10208030 4LBBA1MW

Luminous Intensity Polar Plot





TEST NUMBER: P251973

CATALOG NUMBER: LD4B10D010 EU4B10208030 4LBBA1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	103	96	91	86	101	95	90	85	91	87	83	88	85	82	85	82	80	78			
3	96	87	81	75	94	86	80	75	83	78	73	80	76	72	78	74	71	69			
4	89	80	72	67	87	78	72	66	76	70	65	74	69	65	72	67	64	62			
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	62	58	56			
6	78	67	59	54	77	66	59	54	64	58	53	63	57	53	61	56	53	51			
7	74	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46			
8	69	58	50	45	68	57	50	45	56	49	45	55	49	45	53	48	44	43			
9	65	54	46	42	64	53	46	42	52	46	41	51	45	41	50	45	41	39			
10	62	50	43	39	61	50	43	38	49	43	38	48	42	38	47	42	38	37			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	87654
5°	86746
10°	84147
15°	80767
20°	77131
25°	72133
30°	62794
35°	48458
40°	35851
45°	28213
50°	24229
55°	22038
60°	20076
65°	18587
70°	17182
75°	16116
80°	14929
85°	14089



TEST NUMBER: P251973

CATALOG NUMBER: LD4B10D010 EU4B10208030 4LBBA1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.5	6.5
10°-20°	225.0	17.5
20°-30°	304.4	23.7
30°-40°	255.8	19.9
40°-50°	161.9	12.6
50°-60°	116.3	9.0
60°-70°	80.0	6.2
70°-80°	45.3	3.5
80°-90°	13.9	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	612.9	47.7
0°-40°	868.7	67.5
0°-60°	1146.8	89.2
0°-90°	1286.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1286.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	899	
5°	887	83
15°	800	225
25°	671	304
35°	407	256
45°	205	162
55°	130	116
65°	81	80
75°	43	45
85°	13	14
90°	0	



TEST NUMBER: P251973

CATALOG NUMBER: LD4B10D010 EU4B10208030 4LBBA1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	899.4
2.5°	896.6
5°	886.7
7.5°	870.6
10°	850.3
12.5°	826.5
15°	800.5
17.5°	772.5
20°	743.7
22.5°	710.1
25°	670.8
27.5°	620.4
30°	558.0
32.5°	485.1
35°	407.3
37.5°	338.6
40°	281.8
42.5°	237.6
45°	204.7
47.5°	179.5
50°	159.8
52.5°	143.7
55°	129.7
57.5°	115.7
60°	103.0
62.5°	91.1
65°	80.6
67.5°	70.1
70°	60.3
72.5°	51.2
75°	42.8
77.5°	34.3
80°	26.6
82.5°	19.6
85°	12.6
87.5°	5.6
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)