

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P208155

Luminaire Tested: **LD4B10D010 EU4B10208030 4LBMLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P208155
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B10D010 EU4B10208030 4LBMLI1
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH SPECULAR CLEAR TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1007.2 lumens
Efficiency: N/A
Efficacy: 101.7 lumens/watt
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.76
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P208155

CATALOG NUMBER: LD4B10D010 EU4B10208030 4LBMLI1

Luminous Intensity Polar Plot





TEST NUMBER: P208155

CATALOG NUMBER: LD4B10D010 EU4B10208030 4LBMLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94				
2	109	104	100	97	107	102	99	96	99	96	94	96	94	92	94	92	90	88				
3	104	98	93	89	102	96	92	89	94	90	87	91	88	86	89	87	85	83				
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	79	78				
5	94	87	81	77	93	86	81	77	84	79	76	82	78	75	81	77	75	73				
6	90	82	76	72	89	81	76	72	80	75	71	78	74	71	77	73	71	69				
7	86	77	72	68	85	77	71	68	75	71	67	74	70	67	73	69	67	65				
8	82	73	68	64	81	73	67	64	72	67	64	71	66	63	70	66	63	62				
9	79	70	64	60	78	69	64	60	68	63	60	67	63	60	67	63	60	58				
10	75	66	61	57	74	66	61	57	65	60	57	64	60	57	64	60	57	56				

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P208155

CATALOG NUMBER: LD4B10D010 EU4B10208030 4LBMLI1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	143.8	14.3
10°-20°	321.4	31.9
20°-30°	319.5	31.7
30°-40°	174.0	17.3
40°-50°	40.2	4.0
50°-60°	5.7	0.6
60°-70°	2.1	0.2
70°-80°	0.5	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	784.7	77.9
0°-40°	958.7	95.2
0°-60°	1004.6	99.7
0°-90°	1007.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1007.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1588	
5°	1555	144
15°	1160	321
25°	701	320
35°	269	174
45°	46	40
55°	6	6
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P208155

CATALOG NUMBER: LD4B10D010 EU4B10208030 4LBMLI1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1587.8
2.5°	1584.1
5°	1554.9
7.5°	1495.2
10°	1412.3
12.5°	1290.5
15°	1160.1
17.5°	1030.9
20°	904.2
22.5°	800.6
25°	700.7
27.5°	605.6
30°	498.4
32.5°	379.0
35°	269.3
37.5°	181.6
40°	118.2
42.5°	74.3
45°	46.3
47.5°	26.8
50°	13.4
52.5°	7.3
55°	6.1
57.5°	3.7
60°	3.7
62.5°	2.4
65°	2.4
67.5°	1.2
70°	1.2
72.5°	1.2
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)