

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P755193

Luminaire Tested: LD4D85BD010-EU4DR7070959027-4LBSQW1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P755193
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D85BD010-EU4DR7070959027-4LBSQW1B
Description: 4 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4903.4 lumens
Efficiency: N/A
Efficacy: 55.9 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 87.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P755193
CATALOG NUMBER: LD4D85BD010-EU4DR7070959027-4LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P755193

CATALOG NUMBER: LD4D85BD010-EU4DR7070959027-4LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	602344
5°	584442
10°	568156
15°	560700
20°	523577
25°	393338
30°	278052
35°	98490
40°	51789
45°	55163
50°	57113
55°	58195
60°	58564
65°	57317
70°	54084
75°	50109
80°	44485
85°	36104

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 58565 cd/sqm



TEST NUMBER: P755193

CATALOG NUMBER: LD4D85BD010-EU4DR7070959027-4LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	502.6	10.3
10°-20°	1378.6	28.1
20°-30°	1518.4	31.0
30°-40°	580.1	11.8
40°-50°	273.9	5.6
50°-60°	272.3	5.6
60°-70°	218.0	4.4
70°-80°	125.3	2.6
80°-90°	34.1	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3399.7	69.3
0°-40°	3979.8	81.2
0°-60°	4526.0	92.3
0°-90°	4903.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4903.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5513	
5°	5329	503
15°	4957	1379
25°	3263	1518
35°	738	580
45°	357	274
55°	306	272
65°	222	218
75°	119	125
85°	29	34
90°	0	



TEST NUMBER: P755193

CATALOG NUMBER: LD4D85BD010-EU4DR7070959027-4LBSQW1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	5512.9
2.5°	5455.3
5°	5328.7
7.5°	5223.1
10°	5121.0
12.5°	5034.6
15°	4956.9
17.5°	4769.2
20°	4503.0
22.5°	3928.7
25°	3262.7
27.5°	2840.3
30°	2203.9
32.5°	1423.6
35°	738.4
37.5°	398.9
40°	363.1
42.5°	360.5
45°	357.0
47.5°	349.1
50°	336.0
52.5°	321.2
55°	305.5
57.5°	288.0
60°	268.0
62.5°	245.3
65°	221.7
67.5°	195.5
70°	169.3
72.5°	143.1
75°	118.7
77.5°	93.4
80°	70.7
82.5°	49.8
85°	28.8
87.5°	11.3
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)