

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P207024

Luminaire Tested: **LD4B10D010 EU4B10208030 4LBWMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P207024
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B10D010 EU4B10208030 4LBWMW1
Description: PORTFOLIO 4 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 937.7 lumens
Efficiency: N/A
Efficacy: 94.7 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.09
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P207024

CATALOG NUMBER: LD4B10D010 EU4B10208030 4LBWMW1

Luminous Intensity Polar Plot





TEST NUMBER: P207024

CATALOG NUMBER: LD4B10D010 EU4B10208030 4LBWMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	103	96	91	86	101	94	89	85	91	87	83	88	84	81	85	82	80	78			
3	96	87	80	75	93	85	79	74	83	77	73	80	76	72	78	74	71	69			
4	89	79	72	66	87	78	71	66	75	69	65	73	68	64	71	67	63	61			
5	83	72	64	59	81	71	64	58	69	63	58	67	62	57	65	61	57	55			
6	78	66	58	53	76	65	58	53	64	57	52	62	56	52	60	55	51	50			
7	73	61	53	48	71	60	53	48	59	52	47	57	51	47	56	51	47	45			
8	68	56	49	44	67	56	49	44	54	48	43	53	47	43	52	47	43	41			
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	43	39	38			
10	61	49	42	37	59	48	41	37	47	41	37	46	41	37	46	40	36	35			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P207024

CATALOG NUMBER: LD4B10D010 EU4B10208030 4LBWMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.4	5.7
10°-20°	149.2	15.9
20°-30°	210.9	22.5
30°-40°	204.2	21.8
40°-50°	137.8	14.7
50°-60°	85.5	9.1
60°-70°	57.2	6.1
70°-80°	31.3	3.3
80°-90°	8.3	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	413.4	44.1
0°-40°	617.7	65.9
0°-60°	841.0	89.7
0°-90°	937.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	937.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	568	
5°	563	53
15°	529	149
25°	462	211
35°	328	204
45°	176	138
55°	94	86
65°	57	57
75°	29	31
85°	7	8
90°	0	



TEST NUMBER: P207024

CATALOG NUMBER: LD4B10D010 EU4B10208030 4LBMMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	568.3
2.5°	568.3
5°	563.4
7.5°	557.3
10°	550.0
12.5°	542.7
15°	529.3
17.5°	518.4
20°	500.1
22.5°	481.9
25°	462.4
27.5°	435.6
30°	406.4
32.5°	368.7
35°	328.5
37.5°	288.4
40°	248.2
42.5°	208.1
45°	176.4
47.5°	147.2
50°	125.3
52.5°	107.1
55°	93.7
57.5°	82.7
60°	74.2
62.5°	65.7
65°	57.2
67.5°	49.9
70°	42.6
72.5°	36.5
75°	29.2
77.5°	23.1
80°	17.0
82.5°	12.2
85°	7.3
87.5°	2.4
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)