

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P755119

Luminaire Tested: LD4D85BD010-EU4DR6570959030-4LBCSSQMW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P755119
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D85BD010-EU4DR6570959030-4LBCSSQMW
Description: 4 INCH SQAURE SHALLOW CAST MATTE WHITE TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7262.5 lumens
Efficiency: N/A
Efficacy: 82.8 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 87.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P755119
CATALOG NUMBER: LD4D85BD010-EU4DR6570959030-4LBCSSQMW

Luminous Intensity Polar Plot





TEST NUMBER: P755119

CATALOG NUMBER: LD4D85BD010-EU4DR6570959030-4LBCSSQMW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93																			
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85																			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78																			
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72																			
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66																			
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61																			
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56																			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52																			
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49																			
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	385121
5°	384147
10°	383821
15°	371987
20°	338648
25°	295110
30°	245451
35°	194487
40°	140367
45°	88683
50°	46221
55°	24570
60°	12907
65°	7103
70°	2971
75°	3272
80°	2287
85°	1943

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 88683 cd/sqm



TEST NUMBER: P755119

CATALOG NUMBER: LD4D85BD010-EU4DR6570959030-4LBCSSQMW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	623.6	8.6
10°-20°	1707.6	23.5
20°-30°	2087.3	28.7
30°-40°	1693.6	23.3
40°-50°	844.0	11.6
50°-60°	235.4	3.2
60°-70°	53.5	0.7
70°-80°	13.9	0.2
80°-90°	3.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4418.5	60.8
0°-40°	6112.1	84.2
0°-60°	7191.5	99.0
0°-90°	7262.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7262.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6594	
5°	6552	624
15°	6152	1708
25°	4580	2087
35°	2728	1694
45°	1074	844
55°	241	235
65°	51	54
75°	14	14
85°	3	4
90°	0	



TEST NUMBER: P755119

CATALOG NUMBER: LD4D85BD010-EU4DR6570959030-4LBCSSQMW

CANDELA DISTRIBUTION (FULL):

	0°
0°	6594.1
2.5°	6589.3
5°	6552.4
7.5°	6531.1
10°	6472.0
12.5°	6351.9
15°	6152.2
17.5°	5840.2
20°	5448.7
22.5°	5026.3
25°	4579.5
27.5°	4101.8
30°	3639.6
32.5°	3183.2
35°	2727.8
37.5°	2273.3
40°	1841.1
42.5°	1436.1
45°	1073.7
47.5°	748.1
50°	508.7
52.5°	350.8
55°	241.3
57.5°	162.8
60°	110.5
62.5°	76.6
65°	51.4
67.5°	26.2
70°	17.4
72.5°	16.5
75°	14.5
77.5°	9.7
80°	6.8
82.5°	4.8
85°	2.9
87.5°	1.9
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)