

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P207132

Luminaire Tested: **LD4B10D010 EU4B10209030 4LBMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P207132
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B10D010 EU4B10209030 4LBMH1
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 689.5 lumens
Efficiency: N/A
Efficacy: 69.7 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P207132

CATALOG NUMBER: LD4B10D010 EU4B10209030 4LBMH1

Luminous Intensity Polar Plot





TEST NUMBER: P207132

CATALOG NUMBER: LD4B10D010 EU4B10209030 4LBMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85			
3	101	94	89	85	99	93	88	84	90	86	83	88	84	82	86	83	80	79			
4	96	88	82	77	94	86	81	77	84	80	76	82	78	75	80	77	74	73			
5	90	82	75	71	89	81	75	70	79	74	70	77	73	69	75	72	69	67			
6	86	76	70	65	84	75	69	65	74	68	64	72	68	64	71	67	64	62			
7	81	71	65	60	80	70	64	60	69	64	60	68	63	59	67	62	59	58			
8	77	67	60	56	75	66	60	56	65	59	56	64	59	55	63	58	55	54			
9	73	63	56	52	72	62	56	52	61	56	52	60	55	52	59	55	52	50			
10	69	59	53	49	68	59	53	49	58	52	49	57	52	48	56	52	48	47			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P207132

CATALOG NUMBER: LD4B10D010 EU4B10209030 4LBMH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	62.9	9.1
10°-20°	165.1	23.9
20°-30°	212.1	30.8
30°-40°	159.6	23.1
40°-50°	64.1	9.3
50°-60°	18.2	2.6
60°-70°	5.8	0.8
70°-80°	1.6	0.2
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	440.1	63.8
0°-40°	599.7	87.0
0°-60°	682.0	98.9
0°-90°	689.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	689.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	684	
5°	671	63
15°	589	165
25°	468	212
35°	256	160
45°	79	64
55°	19	18
65°	5	6
75°	1	2
85°	0	0
90°	0	



TEST NUMBER: P207132

CATALOG NUMBER: LD4B10D010 EU4B10209030 4LBMH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	683.8
2.5°	679.6
5°	671.3
7.5°	655.7
10°	635.9
12.5°	612.0
15°	589.1
17.5°	563.1
20°	535.0
22.5°	504.8
25°	468.3
27.5°	424.6
30°	373.6
32.5°	316.4
35°	256.0
37.5°	199.8
40°	149.9
42.5°	110.3
45°	79.1
47.5°	54.1
50°	37.5
52.5°	26.0
55°	18.7
57.5°	13.5
60°	10.4
62.5°	7.3
65°	5.2
67.5°	4.2
70°	3.1
72.5°	2.1
75°	1.0
77.5°	1.0
80°	1.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)