

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P755128

Luminaire Tested: LD4D85BD010-EU4DR6570959030-4LBSQW1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P755128
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D85BD010-EU4DR6570959030-4LBSQW1B
Description: 4 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5432.6 lumens
Efficiency: N/A
Efficacy: 61.9 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 87.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P755128
CATALOG NUMBER: LD4D85BD010-EU4DR6570959030-4LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P755128

CATALOG NUMBER: LD4D85BD010-EU4DR6570959030-4LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	584414
5°	584891
10°	605489
15°	606489
20°	558377
25°	475762
30°	364209
35°	257309
40°	151886
45°	61668
50°	22352
55°	12458
60°	7146
65°	3930
70°	4121
75°	3208
80°	3335
85°	2883

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 61668 cd/sqm



TEST NUMBER: P755128

CATALOG NUMBER: LD4D85BD010-EU4DR6570959030-4LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	515.0	9.5
10°-20°	1485.7	27.3
20°-30°	1782.5	32.8
30°-40°	1197.9	22.1
40°-50°	358.6	6.6
50°-60°	63.3	1.2
60°-70°	18.0	0.3
70°-80°	8.8	0.2
80°-90°	2.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3783.2	69.6
0°-40°	4981.1	91.7
0°-60°	5403.0	99.5
0°-90°	5432.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5432.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5349	
5°	5333	515
15°	5362	1486
25°	3946	1783
35°	1929	1198
45°	399	359
55°	65	63
65°	15	18
75°	8	9
85°	2	3
90°	0	



TEST NUMBER: P755128
CATALOG NUMBER: LD4D85BD010-EU4DR6570959030-4LBSQW1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	5348.8
2.5°	5371.6
5°	5332.8
7.5°	5413.4
10°	5457.5
12.5°	5446.9
15°	5361.7
17.5°	5153.5
20°	4802.3
22.5°	4388.8
25°	3946.4
27.5°	3447.0
30°	2886.8
32.5°	2379.1
35°	1929.1
37.5°	1484.5
40°	1064.9
42.5°	695.5
45°	399.1
47.5°	211.3
50°	131.5
52.5°	91.2
55°	65.4
57.5°	47.1
60°	32.7
62.5°	21.3
65°	15.2
67.5°	13.7
70°	12.9
72.5°	9.9
75°	7.6
77.5°	6.8
80°	5.3
82.5°	3.8
85°	2.3
87.5°	1.5
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)