

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P755132

Luminaire Tested: LD4D85BD010-EU4DR6570959035-4LBCSSQMW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P755132
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D85BD010-EU4DR6570959035-4LBCSSQMW
Description: 4 INCH SQAURE SHALLOW CAST MATTE WHITE TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7338.9 lumens
Efficiency: N/A
Efficacy: 83.7 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct


Input Watts (W): 87.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P755132

CATALOG NUMBER: LD4D85BD010-EU4DR6570959035-4LBCSSQMW

Luminous Intensity Polar Plot





TEST NUMBER: P755132
 CATALOG NUMBER: LD4D85BD010-EU4DR6570959035-4LBCSSQMW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93			93
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85			85
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78			78
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72			72
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66			66
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61			61
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56			56
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52			52
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49			49
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46			46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	389180
5°	388198
10°	387866
15°	375906
20°	342216
25°	298223
30°	248034
35°	196533
40°	141846
45°	89616
50°	46711
55°	24825
60°	13036
65°	7172
70°	3005
75°	3317
80°	2321
85°	1943

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 89616 cd/sqm



TEST NUMBER: P755132

CATALOG NUMBER: LD4D85BD010-EU4DR6570959035-4LBCSSQMW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	630.2	8.6
10°-20°	1725.6	23.5
20°-30°	2109.3	28.7
30°-40°	1711.4	23.3
40°-50°	852.9	11.6
50°-60°	237.9	3.2
60°-70°	54.1	0.7
70°-80°	14.1	0.2
80°-90°	3.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4465.1	60.8
0°-40°	6176.5	84.2
0°-60°	7267.2	99.0
0°-90°	7338.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7338.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6664	
5°	6622	630
15°	6217	1726
25°	4628	2109
35°	2756	1711
45°	1085	853
55°	244	238
65°	52	54
75°	15	14
85°	3	4
90°	0	



TEST NUMBER: P755132

CATALOG NUMBER: LD4D85BD010-EU4DR6570959035-4LBCSSQMW

CANDELA DISTRIBUTION (FULL):

0°	
0°	6663.6
2.5°	6658.7
5°	6621.5
7.5°	6599.9
10°	6540.2
12.5°	6418.8
15°	6217.0
17.5°	5901.7
20°	5506.1
22.5°	5079.2
25°	4627.8
27.5°	4145.0
30°	3677.9
32.5°	3216.7
35°	2756.5
37.5°	2297.2
40°	1860.5
42.5°	1451.2
45°	1085.0
47.5°	756.0
50°	514.1
52.5°	354.5
55°	243.8
57.5°	164.5
60°	111.6
62.5°	77.4
65°	51.9
67.5°	26.4
70°	17.6
72.5°	16.6
75°	14.7
77.5°	9.8
80°	6.9
82.5°	4.9
85°	2.9
87.5°	2.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)