

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206926

Luminaire Tested: **LD4B10D010 EU4B10209030 4LBWB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P206926
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B10D010 EU4B10209030 4LBWB1
Description: PORTFOLIO 4 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH SPECULAR BLACK TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 448.3 lumens
Efficiency: N/A
Efficacy: 45.3 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.08 / 1.03
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P206926

CATALOG NUMBER: LD4B10D010 EU4B10209030 4LBWB1

Luminous Intensity Polar Plot





TEST NUMBER: P206926

CATALOG NUMBER: LD4B10D010 EU4B10209030 4LBWB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93	93	93	93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	86	86	86	86
3	101	94	89	85	99	93	88	84	90	86	83	88	84	82	86	83	80	79	79	79	79
4	96	88	82	77	94	86	81	77	84	79	76	82	78	75	80	77	74	72	72	72	72
5	90	81	75	70	89	80	74	70	79	73	69	77	72	69	75	71	68	67	67	67	67
6	85	76	69	65	84	75	69	64	73	68	64	72	67	64	70	66	63	62	62	62	62
7	80	71	64	60	79	70	64	59	69	63	59	67	62	59	66	62	58	57	57	57	57
8	76	66	60	55	75	65	59	55	64	59	55	63	58	54	62	58	54	53	53	53	53
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	50	49	49	49	49
10	68	58	52	48	67	58	52	48	57	51	47	56	51	47	55	50	47	46	46	46	46

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P206926

CATALOG NUMBER: LD4B10D010 EU4B10209030 4LBWB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	35.3	7.9
10°-20°	100.1	22.3
20°-30°	138.4	30.9
30°-40°	118.5	26.4
40°-50°	50.4	11.2
50°-60°	5.6	1.3
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	273.8	61.1
0°-40°	392.3	87.5
0°-60°	448.3	100.0
0°-90°	448.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	448.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	374	
5°	372	35
15°	356	100
25°	304	138
35°	192	118
45°	63	50
55°	3	6
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P206926

CATALOG NUMBER: LD4B10D010 EU4B10209030 4LBWB1

CANDELA DISTRIBUTION (FULL):

	0°
0°	374.2
2.5°	373.2
5°	372.1
7.5°	370.0
10°	365.9
12.5°	363.8
15°	355.5
17.5°	348.2
20°	336.8
22.5°	323.3
25°	303.5
27.5°	281.7
30°	256.7
32.5°	226.6
35°	192.3
37.5°	157.0
40°	121.6
42.5°	90.4
45°	63.4
47.5°	39.5
50°	22.9
52.5°	11.4
55°	3.1
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)