

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P252062

Luminaire Tested: **LD4B10D010 EU4B10209730 4LBBA1MB**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P252062
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1712-453-4)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B10D010 EU4B10209730 4LBBA1MB
Description: PORTFOLIO 4 INCH BAFFLE RECESSED DOWNLIGHT, WITH MATTE BLACK TRIM
Light Source: (1) HIGH LUMEN LED 97CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 400.0 lumens
Efficiency: N/A
Efficacy: 39.8 lumens/watt
Spacing Criteria (0/90/45): 1.04 / 1.04 / 0.94
Luminous Opening: Circular (Dia: 0.38' x H: 0')
CIE Type: Direct


Input Watts (W): 10.05
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P252062

CATALOG NUMBER: LD4B10D010 EU4B10209730 4LBBA1MB

Luminous Intensity Polar Plot





TEST NUMBER: P252062

CATALOG NUMBER: LD4B10D010 EU4B10209730 4LBBA1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	88	83	79	86	82	78	84	81	77	82	79	77	75			
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70			
6	88	79	73	68	86	78	72	68	76	71	68	75	70	67	74	70	67	65			
7	83	74	68	63	82	73	67	63	72	67	63	71	66	63	69	65	62	61			
8	79	69	63	59	78	69	63	59	68	63	59	67	62	59	66	62	58	57			
9	75	65	59	55	74	65	59	55	64	59	55	63	58	55	62	58	55	53			
10	72	62	56	52	71	61	56	52	61	55	52	60	55	52	59	55	51	50			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	38983
5°	38878
10°	38506
15°	37886
20°	36777
25°	33980
30°	27560
35°	17085
40°	8040
45°	2812
50°	788
55°	527
60°	409
65°	369
70°	285
75°	188
80°	281
85°	0



TEST NUMBER: P252062

CATALOG NUMBER: LD4B10D010 EU4B10209730 4LBBA1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	37.7	9.4
10°-20°	105.5	26.4
20°-30°	141.9	35.5
30°-40°	90.6	22.7
40°-50°	19.3	4.8
50°-60°	2.9	0.7
60°-70°	1.4	0.4
70°-80°	0.6	0.1
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	285.1	71.3
0°-40°	375.7	93.9
0°-60°	397.9	99.5
0°-90°	400.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	400.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	400	
5°	397	38
15°	376	106
25°	316	142
35°	144	91
45°	20	19
55°	3	3
65°	2	1
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P252062

CATALOG NUMBER: LD4B10D010 EU4B10209730 4LBBA1MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	400.0
2.5°	399.5
5°	397.4
7.5°	393.8
10°	389.1
12.5°	382.8
15°	375.5
17.5°	366.1
20°	354.6
22.5°	338.4
25°	316.0
27.5°	284.6
30°	244.9
32.5°	195.8
35°	143.6
37.5°	98.2
40°	63.2
42.5°	37.6
45°	20.4
47.5°	10.4
50°	5.2
52.5°	3.7
55°	3.1
57.5°	2.6
60°	2.1
62.5°	1.6
65°	1.6
67.5°	1.0
70°	1.0
72.5°	0.5
75°	0.5
77.5°	0.5
80°	0.5
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)